



PRODUCT NUMBER
SEE TABLE



mat'l. code	SEE NOTE 3	surface	ISO 1902	tolerance	ISO 406	projection	product family
ltr	ecn no	dr	date	tolerances unless otherwise specified	ISO 1101	INCH/MM	HPC
K	V50266	SAR	9/5/95	angles	.XX±.01/XX±0.3	scale	1:1
L	V82251	HTB	12/28/98	linear	.XXX±.005/XX±0.13		
M	V00253	JWS	1/12/00	0'±2'	.XXX±.0020/XXX±0.051		
N	V05-0513	DAI	10/19/05	dr	D.SHEAFER	1/7/90	
P	M06-0283	MHT	7/27/06	engr	S.CLARK	1/7/90	
R	M07-0136	AGS	2/26/07	chr	S.CLARK	1/7/90	
S	M08-0280	AGS	9/30/08	appd	S.CLARK	1/7/90	
sheet	revision	S	S	S	S		
index	sheet	1	2	3	4		


PRODUCT NUMBER
SEE TABLE

NOTES:

1. PRODUCT NUMBERING CODE:
50003 - X YYY Z LF
LEAD FREE (OPTIONAL)
TAIL LENGTH SEE TABLE
NO. OF POSITIONS SEE NOTE 2
PLATING SEE TABLE
BASE NUMBER


- PRODUCT NUMBERING CODE FOR
SELECT LOAD PART NUMBERS:
50003 - XXYYY LF
LEAD FREE (OPTIONAL)
SEQUENCE NUMBER
ALWAYS 'XX'
BASE NUMBER

- ②. THIS PRODUCT IS CONFIGURED IN SIZES OF
6 THRU 80 COLUMNS IN INCREMENTS OF ONE.
i.e.: 6,7,8,9.....79,80.
- ③. HOUSING MATERIAL: GLASS AND MINERAL FILLED THERMOPLASTIC.
CONTACT MATERIAL: BeCu
- ④. COMPANY NAME, PART NUMBER AND LOT CODE TO
APPEAR ON THIS SURFACE PER BUS-12-108.
- ⑤. LENGTH FORMULAS
DIM A = $.100/2.54 \times \text{NO. OF COLUMNS} + .75/19.1$
DIM B = $.100/2.54 \times \text{NO. OF COLUMNS} + .450/11.43$
DIM C = $.100/2.54 \times \text{NO. OF COLUMNS} - .100/2.54$
6. PRODUCT WITH 'LF' SUFFIX MEETS EUROPEAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATIONS AS
DISCRIBED IN GS-22-008.
7. THIS HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK
TEMPERATURE FOR 10-30 SECONDS IN CONVECTION, INFRA-RED
OR VAPOR PHASE REFLOW OVEN.
- ⑧. DUE TO SPECIAL PLATING, LF NOT AVAILABLE FOR 50003-XX002.
- ⑨. PLATING OPTION:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.



SECTION U-U

SECTION X-X



RECOMMENDED PCB LAYOUT
(ALL HOLES LOCATED ON .100 [2.54] GRID
UNLESS OTHERWISE SPECIFIED)

mat'l. code SEE NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC			
ltr	ecn no	dr	date	tolerances unless otherwise specified					title				
S				angles	linear	XXX4.01/XXX4.3			4 ROW R/A RECEPTACLE				
						XXX4.005/XXX4.013		SOLDER TAIL, 0 GUIDE PIN					
				0°±2'	XXX44.0020/XXX44.0051		scale 1:1		dwg no				
				dr	D.SHEAFER 1/7/90			sheet 2 of 4 size					
				engr	S.CLARK 1/7/90			50003		A3			
				chr	S.CLARK 1/7/90								
				appd	S.CLARK 1/7/90								
sheet index	revision sheet									type	Product	Customer Drawing	

PRODUCT NUMBER
SEE TABLE

50003-XX002 ONLY

	75	70	65	60	55	50	45	40	36
D	D	D	D	D	D	D	D	D	D
C	C	C	C	C	C	C	C	C	C
B	B	B	B	B	B	B	B	B	B
A	A	A	A	A	A	A	A	A	A

35	30	25	20	15	10	5	1	
D	D	D	D	D	D	D	D	D
C	C	C	C	C	C	C	C	C
B	B	B	B	B	B	B	B	B
A	A	A	A	A	A	A	A	A

TERM.
1

NOTES FOR 50003-XX002 ONLY:

- ALL POSITIONS ARE LOADED AS SHOWN.
- COLUMN 1, ROW A IS DESIGNATED AS SIGNAL TERM. 1, AS VIEWED FROM THE MATING FACE.
- SIGNAL DATA FOR 50003-XX002
SIZE 4X 75
TOTAL NUMBER OF POSITIONS: 300
TOTAL NUMBER OF POSITIONS LOADED: 300

ITEM KEY	QTY.	TAIL LENGTH
A	75	.125 / 3.18
B	75	.125 / 3.18
C	75	.125 / 3.18
D	75	.125 / 3.18

mat'l. code SEE NOTE 3		surface ISO 1302	tolerance ISO 406 ISO 1301	projection 	product family HPC
ltr	ec'n no	dr	date	tolerances unless otherwise specified	title
S				angles linear XXX±.01/XX±.03 XXX±.005/XX±.013 XXX±.0020/XXX±0.051	4 ROW R/A RECEPTACLE SOLDER TAIL, 0 GUIDE PIN
				dr D.SHEAFER 1/7/90	dwg no
				engr S.CLARK 1/7/90	sheet 3 of 4
				chr S.CLARK 1/7/90	size A3
				appd S.CLARK 1/7/90	type Product Customer Drawing
sheet index	revision	sheet			

PRODUCT NUMBER	NUMBER OF POSITIONS SEE NOTE 2	TAIL LENGTH	CONTACT PLATING NOTE 9	TAIL PLATING
50003-1YYYY	YYY	.125±.010 / 3.18±0.25	30u" /0.76u Au	TIN/LEAD
50003-1YYYELF	YYY	.125±.010 / 3.18±0.25	30u" /0.76u Au	TIN
50003-1YYYYF	YYY	.145±.010 / 3.68±0.25	30u" /0.76u Au	TIN/LEAD
50003-1YYYFLF	YYY	.145±.010 / 3.68±0.25	30u" /0.76u Au	TIN
50003-1YYYYH	YYY	.180±.010 / 4.57±0.25	30u" /0.76u Au	TIN/LEAD
50003-1YYYYHLF	YYY	.180±.010 / 4.57±0.25	30u" /0.76u Au	TIN
50003-3YYYY	YYY	.125±.010 / 3.18±0.25	50u" /1.27u Au	TIN/LEAD
50003-3YYYELF	YYY	.125±.010 / 3.18±0.25	50u" /1.27u Au	TIN
50003-3YYYYF	YYY	.145±.010 / 3.68±0.25	50u" /1.27u Au	TIN/LEAD
50003-3YYYFLF	YYY	.145±.010 / 3.68±0.25	50u" /1.27u Au	TIN
50003-5YYYY	YYY	.125±.010 / 3.18±0.25	30u" /0.76u GXT	TIN/LEAD
50003-5YYYELF	YYY	.125±.010 / 3.18±0.25	30u" /0.76u GXT	TIN
50003-5YYYYF	YYY	.145±.010 / 3.68±0.25	30u" /0.76u GXT	TIN/LEAD
50003-5YYYFLF	YYY	.145±.010 / 3.68±0.25	30u" /0.76u GXT	TIN
50003-5YYYYH	YYY	.180±.010 / 4.57±0.25	30u" /0.76u GXT	TIN/LEAD
50003-5YYYYHLF	YYY	.180±.010 / 4.57±0.25	30u" /0.76u GXT	TIN
50003-XX002	YYY	.125±.010 / 3.18±0.25	80u" /2.03u Au	TIN/LEAD

NOTE 8

mat'l. code NOTE 8 SEE NOTE 3				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family HPC			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
S				angles	linear	.XX±.01/XX±0.3 XXX±.005/XXX±0.13 XXX±.0020/XXX±0.051		INCH/MM 		4 ROW R/A RECEPTACLE SOLDER TAIL, 0 GUIDE PIN			
				0'±2'				scale 1:1		dwg no 50003 sheet 4 of 4 size A3			
				dr	D.SHEAFER	1/7/90				type Product Customer Drawing			
				engr	S.CLARK	1/7/90							
				chr	S.CLARK	1/7/90							
				appd	S.CLARK	1/7/90							
sheet index	revision sheet												