








SECTION A-A


LEGEND: 6838-• (*) • •

MATERIAL: _____
(.27)/.0106 THK
BLANK=BRASS
A=PHOS BRONZE


— WINDING
A= PER DETAIL A
BLANK= PER DETAIL B

— FORM
BLANK= CHAIN
L= LOOSE

— PLATING
SEE NOTE 2



INTERLEAF



INTERLEAF

102 TO 154 PLTG.		EC NO.: UC2202-4821 DRAWING NO.: 2012/01/04 CHECKED BY: CHIKASHI PER APPR: F53H TH 2012/01/05 2012/02/02		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ±.--- ±.--- 3 PLACES ±.--- ±.010 2 PLACES ±.25 ±.015 1 PLACE ±.036 ±.--- ANGULAR ±1/2°		DIMENSION STYLE IN/MM DRAWN BY: GUZIK CHECKED BY: PATEL APPROVED BY: LENZ DATE: 11/15/89 DATE: 11/15/89 DATE: 11/15/89		SCALE --- DESIGN UNITS INCH THIRD ANGLE PROJECTION		SHEET NO. 1 OF 2	
DRN: MASHROTH CR: CHIKASHI PER APPR: F53H TH		DESCRIPTION 102 TO 154 PLTG. CRIMP TYPE, .156 CENTERS 18 TO 20 AWG WIRE MOLEX INCORPORATED		MATERIAL NO. SEE CHART DOCUMENT NO. SD-6838		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE D THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		MOLEX MOLEX INCORPORATED		SHEET NO. 1 OF 2	

	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	
M	6838-(*)**					6838-A(*)**															M
	PART NO.	ENG. NO.				PART NO.	ENG. NO.														
	08-50-0187	6838-(P909)		SEE NOTE 1		08-58-0187	6838-A(P558)														
	08-50-0189	6838-(P909)L		SEE NOTE 1		08-58-0189	6838-A(P558)L														
	08-50-0275	6838-(P909)-A				08-52-0112	6838-A(P909)		SEE NOTE 1												
L						08-52-0113	6838-A(P909)L		SEE NOTE 1												L
						08-50-0024	6838-A(154)														
						08-50-0251	6838-A(154)L														
						08-58-0105	6838-A(P555)														
K						08-58-0106	6838-A(P555)L														K
						08-58-0110	6838-A(P56 I)		SEE NOTE 1												
						08-58-0111	6838-A(P56 I)L		SEE NOTE 1												
						08-58-0118	6838-A(56 I)														
						08-58-0119	6838-A(56 I)L														
J																					J
I																					I
H																					H
G																					G
F																					F
E																					E
D																					D
C																					C
B																					B
A																					A

NOTES:
1. PART MANUFACTURED WITH ALTERNATE GEOMETRY. SEE SHEET 1.

SEE SHEET 1 EC NO. UCP2012-1821 DRAWN BY: CHYKMK/PEER CHKD BY: CHYKMK/PEER APPROVED BY: FSMT/TH AR	REV DESCRIPTION 2012/01/04 2012/01/05 2012/02/02	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
					mm	INCH	DRAWN BY GUZIK	DATE 11/15/89		TITLE TRIFURCON TERMINAL CRIMP TYPE .156 CENTERS 18 TO 20 AWG WIRE	
			4 PLACES	±---	±---	CHECKED BY PATEL	DATE 11/15/89				
			3 PLACES	±---	±---	APPROVED BY LENZ	DATE 11/15/89				
			2 PLACES	±---	±---						
					1 PLACE	±---	±---				
					ANGULAR ±1/2°						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE CHART		DOCUMENT NO. SD-6838			SHEET NO. 2 OF 2	
					SIZE D	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					