

500-068
D-Subminiature
Dummy Stowage Receptacle



MIL-C-24308
D-Subminiature




TABLE I: SHELL SIZE & STOWAGE RECEPTACLE DIMENSIONS

Shell Size	Com'l Shell Size Ref	A	B Min	C ±.005 (.1)	D Max	E
1	E/09	1.213 (30.8)	.661 (16.8)	.984 (25.0)	.324 (8.2)	.494 (12.5)
2	A/15	1.541 (39.1)	.989 (25.1)	1.312 (33.3)	.324 (8.2)	.494 (12.5)
3	B/25	2.088 (53.0)	1.529 (38.8)	1.852 (47.0)	.324 (8.2)	.494 (12.5)
4	C/37	2.729 (69.3)	2.177 (55.3)	2.500 (63.5)	.324 (8.2)	.494 (12.5)
5	D/50	2.635 (66.9)	2.074 (52.7)	2.406 (61.1)	.436 (10.9)	.605 (15.4)
6	F/104	2.729 (69.3)	2.207 (56.1)	2.500 (63.5)	.498 (12.4)	.668 (17.0)