






PRODUCT NUMBER SEE SHEET 2




spec ref *				dr	Peng-Bing Fu	2011/04/06	projection 	MM 	size	A3	scale	3:2	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Peng-Bing Fu	2012/11/13			ecn no				ELX-DG-013147-1
ASME Y14.5				chr	Shao-Qi Kuang	2012/11/13			rel level				Released
				appr	Pei-Ming Zheng	2012/11/13			product family				PwrBlade+
surface 	linear	0.X	±0.5		title 3HP + 24S + 3HP RA STB HEADER				dwg no	10106124-6006001			rev B
		0.XX	±0.25										
		0.XXX	±0.10										
ASME Y14.5	angular	0°	±2°	www.fci.com	cat. no.			Product - Customer Drw				sheet 1 of 3	



Copyright FCI.

PRODUCT NO.	ROWS	HIGH POWER				SIGNAL						HIGH POWER			
		E1	P1	P2	P3	1	2	3	4	5	6	P4	P5	P6	E2
10106124-6006001LF	D C B A		H1	X	H1	X	X	X	U	U	X	H1	H1	H1	
						X	X	X	S	S	X				
						X	X	X	R	R	X				



CODE	DESCRIPTION
HI	STD HIGH POWER CONTACT (3.43)
HA	METAL HOLD DOWN
R	STD SIGNAL CONTACT, ROW A (3.43)
S	STD SIGNAL CONTACT, ROW B (3.43)
T	STD SIGNAL CONTACT, ROW C (3.43)
U	STD SIGNAL CONTACT, ROW D (3.43)
X	OMITTED

dr	Peng-Bing Fu	2011/04/06	projection	MM	size	A3	scale	3:2		
eng	Peng-Bing Fu	2012/11/13			ecn no	ELX-DG-013147-1				
chr	Shao-Qi Kuang	2012/11/13			rel level			Released		
appr	Pei-Ming Zheng	2012/11/13	product family		PwrBlade+					
		title			3HP + 24S + 3HP		dwg no	10106124-6006001	rev	B
www.fci.com		cat. no.		Product - Customer Drw				sheet 2 of 3		
RA STB HEADER										

A

B

C

D

A

B

C


D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE P/N CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ± 0.025 MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ± 0.07 MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.
- 9) A  SYMBOL WILL BE NEXT TO ANY DIMENSION,VIEW,OR NOTE WHICH HAS BEEN
MODIFIED WITH THE CURRENT DRAWING REVISION.



Copyright FCI.

dr	Peng-Bing Fu	2011/04/06	projection 	MM 	size	scale	
eng	Peng-Bing Fu	2012/11/13			A3	3:2	
chr	Shao-Qi Kuang	2012/11/13					
appr	Pei-Ming Zheng	2012/11/13	product family		PwrBlade+	ecn no	ELX-DG-013147-1
					rel level	Released	
			3HP + 24S + 3HP			rev	
RA STB HEADER			10106124-6006001			B	
www.fci.com			cat. no.			Product - Customer Drw	sheet 3 of 3