


D-Sub Connectors Male

156-1209T-E, 156-1215T-E,
156-1225T-E, 156-1237T-E

KOBICONN

D-Sub Connectors Male

156-1209T-E, 156-1215T-E, 156-1225T-E, 156-1237T-E



MOUSER STOCK NO.	Position	A	B	C	D
156-1209T-E	9M	16.92	25.00	30.80	19.20
156-1215T-E	15M	25.25	33.30	39.20	27.70
156-1225T-E	25M	38.96	47.10	53.10	41.10
156-1237T-E	37M	55.42	63.50	69.40	57.30

Dimensions: mm

MATERIAL SPECIFICATIONS

Insulator:	Thermal Plastic
Contacts:	Copper Alloy
Shell:	Steel
Rivet, Boardlock:	Copper Alloy, Contact Plating
Underplated:	50μ"~50μ" Nickel
Contact Area:	1μ"~50μ" Selective Gold
Solder Tails Area:	100μ"~200μ" Tin/Lead (Brighten Tin) or 100μ"~200μ" Tin/Lead Free (Brighten Tin/Matte Tin)

ELECTRICAL SPECIFICATIONS

Operation Voltage:	250 VAC Max.
Current Rating:	3 Amps Max.
Contact Resistance:	15 MΩ Max.
Insulation Resistance:	3000 MΩ Min. @ 500 VDC
Dielectric Withstanding Voltage:	1000 VAC / Minute
Temperature Range:	-55°C +105°C

RoHS Compliant

Date Last Revised: 6-13-12

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301313

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.