



Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51721- A00CCDDEF..
NOTE ①
SEE NOTE 1



THIS FILE WAS ORIGINALLY CREATED IN THE PRO ENGINEER ENVIRONMENT AND ANY FUTURE REVISIONS TO THIS FILE MUST BE MADE IN THE PRO ENGINEER ENVIRONMENT

mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER COPY		FCI www.fciconnect.com	
litr	ecr no.	dr	date	linear	.XX±.01/.X±.3	projection		title RIGHT ANGLE HEADER w/GUIDE PIN SIGNAL / POWER	
H	DG05-0132	SJ	06/02/05		.XXX±.005/.XX±.13				
J	DG05-0479	CS	11/18/05		.XXXX±.0020/.XXX±.051				
K	DG06-0011	CS	01/13/06	angles	0°±2°				
L	DG06-0252	JMG	06/27/06	dr	D.BOGLE 05-13-99	INCH / MM		product family	PWRBLADE
M	DG06-0367	JULIA	09/07/06	enrg	J. BROWN 05-13-99	scale		size	dwg no
N	DG08-0239	JC	09/11/08	chr	J. BROWN 05-13-99	1:1		51721	213
				appd	J. BROWN 05-13-99				
sheet index		revision sheet	N	N	N				
			1	2	3				

form no. 7530-001-103

cage code
22526

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51721- A00CCCDDEF-- NOTE ①
SEE NOTE 1

1	2										3	4
DIM		LENGTH FORMULAS (SEE NOTE 10)										
DIM "A"		.100 [2.54] x (CCC/4) + .250 [6.35] x DD + .650 [16.51](NOTE 10)										
DIM "B"		.100 [2.54] x (CCC/4) + .250 [6.35] x DD + .350 [8.89]										
DIM "C"		.100 [2.54] x (CCC/4) + .250 [6.35] x DD + .300 [7.62]										
DIM "E"		.100 [2.54] x (CCC/4) + .450 [11.43]										
DIM "F"		.100 [2.54] x (CCC/4) + .250 [6.35] x DD + .680 [17.27]										
DIM "H"		.100 [2.54] x (CCC/4) + .250 [6.35]										

CONNECTOR NOTES

- ① PRODUCT NUMBER CODE:
51721 - A 00 CCC DD E F LF
- NO THIS SUFFIX: 100u"/2.54um SnPb ON PCB INTERFACE
ADD THIS SUFFIX: 78u"/2.00um Sn ON PCB INTERFACE ⚠
- RETENTION TO PCB (NOTE 8)
TAIL OPTIONS (NOTE 7)
NUMBER OF RIGHT END POWER CONTACTS (NOTE 6)
NUMBER OF SIGNAL CONTACTS (NOTE 5)
ALWAYS ZERO (NOTE 4)
PLATING (NOTE 3)
BASE NUMBER
- ② HOUSING MATERIAL: GLASS FILLED V-O HIGH TEMP THERMO PLASTIC.
SIGNAL CONTACT MATERIAL: COPPER ALLOY
POWER CONTACT MATERIAL: COPPER ALLOY
- ③ PLATING OPTION:
A = SEE PRINT 10064183 FOR PLATING SPEC OF 51721-100CCCDDEF; 51721-100CCCDDEFLF
- ④ THIS PART NOT AVAILABLE WITH LEFT SIDE POWER CONTACTS.
- ⑤ SIGNAL CONTACTS, 004 TO 148 AVAILABLE.
- ⑥ RIGHT END POWER CONTACTS, 01 TO 20 AVAILABLE.
MAXIMUM OF 20 POWER CONTACTS PER CONNECTOR.
- ⑦ TAIL OPTIONS:
A = .135 [3.43] SOLDER TO BOARD

- ⑧ RETENTION TO PCB OPTIONS:
A = BOARD LOCK (REQUIRES .098 + .002, -.001
[2.49 +0.05, -0.03] THRU HOLE IN PCB).
MOUNTING FOOT THICKNESS: .220[5.59]
B = .150 [3.81] THRU HOLE (REQUIRES .158±.003
[4.01±08] THRU HOLE IN PCB).
MOUNTING FOOT THICKNESS: .160[4.06]
- ⑨ MANUFACTURE'S NAME, P/N, AND DATE CODE
TO APPEAR ON THIS SURFACE.
- ⑩ THE MAXIMUM OVERALL LENGTH (DIM A) OF A PART
IS 8.00 [203.2]
11. PRODUCT SPECIFICATION GS-12-149
12. REFERENCE 51730 FOR SELECT LOAD/FMLB WORKSHEET

PCB NOTES:

13. ALL DIMENSIONS ARE BASIC UNLESS OTHERWISE SPECIFIED.
14. ALL THROUGH HOLES ARE LOCATED WITH A
TRUE POSITION OF .004[0.10]
15. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
16. Ø0.0453 ±.001 [1.151 ±0.02] DRILLED HOLES PLATED WITH
0.0003 [0.007] MIN SnPb OR Sn OVER 0.001 [1.03] TO
.003 [0.08] PLATING TO ACHIEVE A .040±.003 [1.02±08] HOLE.
17. A ⚠ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE
WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

THIS FILE WAS ORIGINALLY CREATED IN THE PRO
ENGINEER ENVIRONMENT AND ANY FUTURE REVISIONS TO
THIS FILE MUST BE MADE IN THE PRO ENGINEER
ENVIRONMENT

mat'l code				tolerances unless otherwise specified		CUSTOMER COPY		FCI www.fciconnect.com	
ltr	ecn no.	dr	date	linear	.XX±.01/.X±.3	projection 	title RIGHT ANGLE HEADER w/GUIDE PIN SIGNAL / POWER	product family PWRBLADE	code 213
N					.XXX±.005/.XX±.13				
					.XXX±.0020/.XX±.051				
				angles	0°±2°	INCH / MM scale 1:1	size A	dwg no 51721	SHEET 2 OF 3
				dr	C.BAROT 05-04-99				
				enr	J. BROWN 05-04-99				
				chr	J. BROWN 05-04-99				
				appd	J. BROWN 05-04-99				
sheet index				revision sheet					

form no. 7530-001-103

1 2

3

cage code
22526





4

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51721- A00CCDDEF__
NOTE ①



mat'l code				tolerances unless otherwise specified		CUSTOMER COPY		FCI		www.fciconnect.com	
ltr	ecn no.	dr	date	linear	.XX±.01/.X±.3	projection		title		RIGHT ANGLE HEADER w/GUIDE PIN	
N					.XXX±.005/.XX±.13			SIGNAL / POWER			
				angles	.XXX±.0020/.XXX±.051			product family		PWRBLADE	
				dr	0°±2°	INCH / MM		size		213	
				enr	J. BROWN 05-13-99	scale	1:1	dwg no		51721	
				chr	J. BROWN 05-13-99					SHEET 3 OF 3	
				appd	J. BROWN 05-13-99						
sheet index	revision sheet										

form no. 7530-001-103

cage code 22526