

REVISIONS AR

DO NOT SCALE
FROM THIS PRINT




TABLE 1


TERMINAL STYLE	TERMINAL/BODY SPECIFICATION				FIG.	SHEET
	TS: SINGLE	TS BODY	TD: DOUBLE	TD BODY		
-AA	T-1R5-X	SEE NOTE 7	T-1R5-X	SEE NOTE 6	1	2
-A	T-1R0-X	SEE NOTE 7	T-1R0-X	SEE NOTE 6	2	2
-A-1	T-1R7-1-X	SEE NOTE 7	T-1R7-1-X	SEE NOTE 6	3	2
-A-2	T-1R7-2-X	SEE NOTE 7	T-1R7-2-X	SEE NOTE 6	4	2
-B	T-1R1-X	SEE NOTE 10	T-1R1-X	SEE NOTE 6	5	2
-B-1	T-1R8-1-X	SEE NOTE 7	T-1R8-1-X	SEE NOTE 6	6	2
-B-2	T-1R8-2-X	SEE NOTE 7	T-1R8-2-X	SEE NOTE 6	7	2
-C	T-1R2-X	SEE NOTE 7	T-1R2-X	SEE NOTE 6	8	2
-C-1	T-1R9-1-X	SEE NOTE 7	T-1R9-1-X	SEE NOTE 6	9	2
-C-2	T-1R9-2-X	SEE NOTE 7	T-1R9-2-X	SEE NOTE 6	10	2
-D-1-1	T-1S4-1-1-X	SEE NOTE 7	T-1S4-1-1-X	SEE NOTE 6	11	3
-D-1-2	T-1S4-1-2-X	SEE NOTE 7	T-1S4-1-2-X	SEE NOTE 6	12	3
-D-2-1	T-1S4-2-1-X	SEE NOTE 7	N/A		13	3
-D-2-2	T-1S4-2-1-X	SEE NOTE 7	N/A		14	3
-D-3-2	T-1S4-3-1-X	SEE NOTE 7	N/A		15	3
-D-4-2	T-1S4-4-1-X	SEE NOTE 7	N/A		16	3
-E	T-1R12-X	SEE NOTE 7	N/A		17	3
-F	T-1S5-X	SEE NOTE 7	T-1S5-X	SEE NOTE 6	18	3
-G-1	T-1R5-1-X	SEE NOTE 7	T-1R5-1-X	SEE NOTE 6	19	3
-J	S-1P1-X	SEE NOTE 8	S-1P1-X	DSB-36	21	4
-K	T-1R12-X	SEE NOTE 7	T-1R12-X	SEE NOTE 6	22	4
-L-1	S-1W1-1-X	SEE NOTE 8	S-1W1-1-X	DSB-36	23	4
-L-2	S-1W1-2-X	SEE NOTE 8	S-1W1-2-X	DSB-36	24	4
-L-3	S-1W1-3-X	SEE NOTE 8	S-1W1-3-X	DSB-36	25	4
-M	T-1S2-X	SEE NOTE 8	T-1S2-X	DSB-36	26	4
-N	T-1R5-1-X	SEE NOTE 7	N/A		27	4
-Q-3 *	S-1W1-3-X	SEE NOTE 7	N/A		29	4

N/A = NOT AVAILABLE * STYLE -Q-3 AVAILABLE ONLY AS A COMPONENT
OF CSP/25 CABLE ASSEMBLIES.

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS
ELECTRONIC OR MECHANICAL,
INCLUDING PHOTOCOPYING, RECORDING,
OR BY ANY INFORMATION STORAGE
AND RETRIEVAL SYSTEM, WITHOUT THE
WRITTEN CONSENT OF SAMTEC INC.

DIMENSIONS ARE IN INCHES		TOLERANCES ARE:		ANGLES ± 2°	TITLE: TERMINAL STRIP ASSEMBLY	DWG NO: TX-1XX-X-X SHEET 1 OF 4
ONE PLACE DECIMALS ±	THREE PLACE DECIMALS ±	FOUR PLACE DECIMALS ±				
TWO PLACE DECIMALS ±						



BODY SPEC.	LEAD STYLE	TUBE	PLUG
TS	A-1, A-2, A, AA, B, C, H, G-1, B-1	PT-1-24-01-24	TP-24
	J	PT-1-24-01-23	TP-12
	G-2, D-1-2	PT-1-24-02-03	TP-24
	D-1-1	PT-1-24-10-03	TP-03
TD	A-1	PT-1-24-05-17	TP-07
	A-2	PT-1-24-02-46	
	A, AA	PT-1-24-01-22	TP-03
	J	PT-1-24-01-14	

- NOTE:
- SEE COMPONENT PRINT FOR MAXIMUM ALLOWABLE BOW.
 - MINIMUM PUSHOUT FORCE = 5 LBS.
 - MAXIMUM ALLOWABLE TOE IN/OUT OF TERMINALS = ± 2°.
 - .005 [0.13] MAX. ALLOWABLE FLASH AFTER REMOVAL OF CROSS BARS.
 - Ø REPRESENTS A CRITICAL DIMENSION.
 - USE DSB-36 AND FILL WITH COUNTERBORE DOWN.
 - USE TBS-32 AND FILL WITH COUNTERBORE UP.
 - USE SSB-XX AND FILL WITH COUNTERBORE UP.
 - FOR LEAD STYLES PACKAGED IN TUBES: PACKAGE -05 THRU
-36 POSITIONS IN TUBES: LAYER PACKAGE SMALLER POSITIONS.
 - USE SSB-XX AND FILL WITH COUNTERBORE DOWN.

MATERIAL: INSULATOR: GLASS FILLED POLYESTER COLOR: BLACK	EXISPROD\ASSEMBLY\100 TX-MKT1	
	520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150 PHONE (812) 944-6733 P.O. BOX 1147 CODE 55322	
TERMINAL: BRASS, EXCEPT STYLE G IS PHOSPHOR BRONZE	MADE BY: L.W. 12/05/84	TX-1XX-X-X SHEET 1 OF 4
PLOT SCALE: 1=1		