

SPECIFICATIONS:

MATERIAL:-

BASE: LCP, NATURAL COLOR

COVER: SUS, T=0.15mm

TERMINAL: C5210-H, T=0.20mm

FINISH:-

COVER: Sn

TERMINAL: SELECTED Au/Sn-Cu


ELECTRICAL:-

CONTACT RESISTANCE: 40 mΩ MAX


INSULATION RESISTANCE: 100 MΩ MIN

LEAD CO-PLARITY: 0.1mm MAX

NOTES: ALL DIMENSIONS AND NOTES
 MARKED **X** ARE CRITICAL AND
 MUST BE CHECKED IN ACCORDANCE
 WITH QUALITY DOC. Q1-02A



OBSOLETE



TOLERANCES		
X. = ±0.25mm		
X.X = ±0.2mm		
X.XX = ±0.15mm		

HARWIN

HARWIN USA
 TEL: 603 893 5376
 FAX: 603 893 5396
 mis@harwin.com

HARWIN Europe (UK)
 TEL: 023 9231 4545
 FAX: 023 9231 4590
 mis@harwin.co.uk

HARWIN Asia
 TEL: +65 6 779 4909
 FAX: +65 6 779 3868
 mis@harwin.com.sg

THIS DRAWING AND ANY
 INFORMATION OR DESCRIPTIVE
 MATTER SET OUT HEREON ARE
 CONFIDENTIAL AND COPYRIGHT
 PROPERTY OF THE HARWIN
 GROUP AND MUST NOT BE
 DISCLOSED, LOANED, COPIED
 OR USED FOR MANUFACTURING,
 TENDERING OR FOR ANY
 OTHER PURPOSE WITHOUT
 THEIR WRITTEN PERMISSION.

TOLERANCES
 X. = ±1mm
 X.X = ±0.25mm
 X.XX = ±0.1mm
 X.XXX = ±0.01mm
 ANGLES = ±5°
 UNLESS STATED

MATERIAL:
 SEE NOTES
 FINISH:
 SEE NOTES
 S/AREA: mm²

TITLE:
 LVDS 30 PIN RECEPTACLE (REVERSE)
 DRAWING NUMBER:
 M711-2103042R
 SHT 1 OF 1

NAME	ISS.	DATE	C/NOTE
APPROVED: <i>Bob</i>			
CHECKED:			
DRAWN: Allan			
CUSTOMER REF.:			
ASSEMBLY DRG.:			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Harwin:](#)

[LVDS-301P](#)