




Telecommunication HDSL Transformer Transformers

DT31-2019AS
DT31-2020AS
DT31-2021AS
DT31-2033AS



DIMENSIONS IN mm

A	B	C	D	E	F	G
12.5 MAX.	14.0 MAX.	17.10±0.2	254±0.3	14.0 MAX.		

ELECTRICAL CHARACTERISTICS

	DT31-2019AS	DT31-2020AS	DT31-2021AS	DT31-2033AS
T.R	(PRI:SEC): 1.8:1±1% @10KHz 0.1V	(PRI:SEC): 1.8:1±1% @10KHz 0.1V	(PRI:SEC): 1.8:1±1% @10KHz 0.1V	(PRI:SEC): 1.8:1±1% @10KHz 0.1V
L	PRI: 2.92mH±5% @10KHz 0.1V	PRI: 2.92mH±5% @10KHz 0.1V	SEC: 600uH±5% @10KHz 0.1V	PRI: 3.0mH±10% @10KHz 0.1V
L.K	-----	-----	PRI: 20uH Max. @100KHz 0.1V	PRI: 30uH Max. @100KHz 0.1V
D.C.R	N1: 2.11Ω±10% N2: 2.11Ω±10% N3: 2.63Ω±10%	N1: 1.60Ω±10% N2: 1.60Ω±10% SEC: 1.78Ω±10%	N1: 3.50Ω±10% N2: 3.50Ω±10% N3: 3.17Ω±10%	N1: 1.5Ω Max. N2: 1.5Ω Max. SEC: 2.3Ω Max.
HI-POT	1500 VAC 1 SEC	1500 VAC 1 SEC	1500 VAC 1 SEC	2000 VAC 1 SEC
C	-----	-----	75pF Max. @100KHz 0.1V	-----
I.L	-----	-----	-----	-----
L.B	50dB Min. @40KHz~300KHz	50dB Min. @40KHz~300KHz	53dB Min. @500Hz~292KHz	50dB Min. @5kKHz~196KHz
FR	-----	-----	-----	-----
R.L	-----	-----	-----	16.5 dB Min. @40KHz~200KHz
T.H.D	-80 dB Typ. @5KHz 5Vp-p	-80 dB Typ. @5KHz 5Vp-p	-84.5 dB Typ. @5KHz 1.45Vrms	-75 dB Typ. @5KHz 5Vp-p
SCHEMATIC	2	1	2	3

DELTA ELECTRONICS, INC.

(TAOYUAN PLANT CPBG) 31-1, SHIEN PAN ROAD, KUEI SAN INDUSTRIAL ZONE, TAOYUAN SHIEN, TAIWAN, R.O.C.
TEL: 886-3-3626301 FAX: 886-3-3618901
<http://www.deltaww.com>