

Surface-Mount Schottky Barrier Rectifier



SMA (DO-214AC)

Cathode  Anode

LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS	
$I_{F(AV)}$	1.5 A
V_{RRM}	90 V
I_{FSM}	40 A
V_F	0.75 V
T_J max.	150 °C
Package	SMA (DO-214AC)
Circuit configuration	Single

FEATURES

- Low profile package
- Ideal for automated placement
- Guardring for overvoltage protection
- Low power losses, high efficiency
- Very low switching losses
- High surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

TYPICAL APPLICATIONS

For use in high frequency inverters, switching power supplies, freewheeling diodes, OR-ing diode, DC/DC converters and reverse battery protection.

MECHANICAL DATA

Case: SMA (DO-214AC)

Molding compound meets UL 94 V-0 flammability rating
Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes the cathode end

MAXIMUM RATINGS ($T_A = 25\text{ °C}$ unless otherwise noted)			
PARAMETER	SYMBOL	BYS11-90	UNIT
Device marking code		BYS109	
Maximum repetitive peak reverse voltage	V_{RRM}	90	V
Maximum average forward rectified current	$I_{F(AV)}$	1.5	A
Peak forward surge current single half sine-wave superimposed on rated load	I_{FSM}	40	A
		30	
Voltage rate of change (rated V_R)	dV/dt	10 000	V/ μ s
Junction and storage temperature range	T_J, T_{STG}	-55 to +150	°C

**ELECTRICAL CHARACTERISTICS** ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	BYS11-90	UNIT
Maximum instantaneous forward voltage	1.0 A	$V_F^{(1)}$	750	mV
Maximum DC reverse current	V_{RRM}	$T_J = 25\text{ }^{\circ}\text{C}$	100	μA
		$T_J = 100\text{ }^{\circ}\text{C}$	1	mA

Note

⁽¹⁾ Pulse test: 300 μs pulse width, 1 % duty cycle

THERMAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	BYS11-90	UNIT
Maximum thermal resistance, junction to lead	$R_{\theta JL}$	25	$^{\circ}\text{C/W}$
Maximum thermal resistance, junction to ambient	$R_{\theta JA}^{(1)}$	150	$^{\circ}\text{C/W}$
	$R_{\theta JA}^{(2)}$	125	
	$R_{\theta JA}^{(3)}$	100	

Notes

⁽¹⁾ Mounted on epoxy-glass hard tissue

⁽²⁾ Mounted on epoxy-glass hard tissue, 50 mm² 35 μm Cu

⁽³⁾ Mounted on Al-oxide-ceramic (Al_2O_3), 50 mm² 35 μm Cu

ORDERING INFORMATION (Example)

PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
BYS11-90-M3/TR	0.064	TR	1800	7" diameter plastic tape and reel
BYS11-90-M3/TR3	0.064	TR3	7500	13" diameter plastic tape and reel


RATINGS AND CHARACTERISTICS CURVES ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)


Fig. 1 - Typical Instantaneous Forward Characteristics




Fig. 4 - Typical Reverse Characteristics




Fig. 2 - Max. Average Forward Current vs. Ambient Temperature




Fig. 5 - Max. Reverse Power Dissipation vs. Junction Temperature




Fig. 3 - Max. Average Forward Current vs. Ambient Temperature





Fig. 6 - Diode Capacitance vs. Reverse Voltage




PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

SMA (DO-214AC)



Mounting Pad Layout





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.