


3M™ MEDIUM FLEX LIFE FLAT CABLE, HF539
.050" 28 AWG STRANDED, MEDIUM FLEX LIFE, HALOGEN FREE PO



Note: Available in standard 100 ft and 300 ft rolls, please specify when ordering.
Contact 3M for availability of additional conductor counts and/or custom roll lengths.

- | | |
|----|---|
| 1. | <p>MATERIAL:</p> <p>A) PRIMARY INSULATION: HALOGEN FREE POLYOLEFIN (PO).</p> <p>B) CONDUCTORS: 28 AWG, 19 X 40 AWG (19 X , Ø 0.079), TINNED STRANDED COPPER.</p> |
| 2. | <p>REGULATORY INFORMATION:</p> <p>ROHS COMPLIANT. SEE THE REGULATORY INFORMATION APPENDIX (RIA) IN THE "ROHS COMPLIANCE" SECTION OF WWW.3MCONNECTORS.COM FOR COMPLIANCE INFORMATION (RIA E1 & C1 APPLY)</p> <p>UL FILE NO: E42769,
UL STYLE NO: 21682.</p> |
| 3. | <p>MARKINGS:</p> <p>STANDARD: NONE</p> <p>CANADIAN: SEE "PRINTING ILLUSTRATION" VIEW</p> <p>PRIMARY CABLE: BLUE MARK ON EDGES DESIGNATES WIRE NUMBER 1.</p> |
| 4. | <p>THE SURFACE DEFINED BY THE "ZIP" PROCESS IS NOT REQUIRED TO BE BLUE.</p> |
| 5. | <p>ENVIRONMENTAL:</p> <p>TEMP RATING: -40°C TO 105°C</p> <p>FLAMABILITY RATING: HORIZONTAL.</p> |
| 6. | <p>HALOGEN FREE IS DEFINED AS BOTH:</p> <p>1) NO HALOGEN COMPOUNDS THAT ARE INTENTIONALLY ADDED TO THE PRODUCT OR USED IN THE MANUFACTURING PROCESS FOR THE PRODUCT.</p> <p>2) ANY IMPURITIES PRESENT ARE LESS THAN 900 ppm BROMINE, LESS THAN 900 ppm CHLORINE AND/OR LESS THAN 1500 ppm TOTAL BROMINE AND CHLORINE. THE LATTER ARE THE LEVELS SET FORTH IN CERTAIN INDUSTRY STANDARDS FOR PRINTED CIRCUIT BOARDS, SUCH AS THE INTERNATIONAL ELECTROTECHNICAL COMMISSION (IEC) 61249-2-21 STANDARD. THIS INFORMATION REPRESENTS 3M/S KNOWLEDGE AND BELIEF WHICH MAY BE BASED IN WHOLE OR IN PART ON INFORMATION PROVIDED BY 3RD PARTY SUPPLIERS TO 3M.</p> |

TABLE 1
DIMENSION CHART

NUMBER OF CONDUCTORS	3M PART NUMBER	DIMENSION 'A' ± AS NOTED	DIMENSION 'B' (SEE NOTE 2)
6	HF539/06	0.300"±0.010"	0.250"±0.007"
9	HF539/09	0.450"±0.010"	0.400"±0.007"
10	HF539/10	0.500"±0.010"	0.450"±0.007"
14	HF539/14	0.700"±0.010"	0.650"±0.007"
15	HF539/15	0.750"±0.010"	0.700"±0.007"
16	HF539/16	0.800"±0.015"	0.750"±0.011"
20	HF539/20	1.000"±0.015"	0.950"±0.011"
24	HF539/24	1.200"±0.015"	1.150"±0.011"
25	HF539/25	1.250"±0.015"	1.200"±0.011"
26	HF539/26	1.300"±0.015"	1.250"±0.011"
30	HF539/30	1.500"±0.020"	1.450"±0.015"
34	HF539/34	1.700"±0.020"	1.650"±0.015"
36	HF539/36	1.800"±0.020"	1.750"±0.015"
37	HF539/37	1.850"±0.020"	1.800"±0.015"
40	HF539/40	2.000"±0.020"	1.950"±0.015"
50	HF539/50	2.500"±0.020"	2.450"±0.015"
60	HF539/60	3.000"±0.020"	2.950"±0.015"
64	HF539/64	3.200"±0.020"	3.150"±0.015"

X HF539/XX XX
 BLANK = STANDARD
 C = CANADIAN
 NUMBER OF CONDUCTORS
 (SEE TABLE 1)
 BLANK = STANDARD
 SF = SPLICE FREE

TABLE 2
ELECTRICAL CHARACTERISTICS

VOLTAGE RATING	USA: 300V, CANADA: 150V, EU: 50V	
INSULATION RESISTANCE	PRIMARY CABLE >1 X 10 ¹⁰ Ω /10 FT [3 m]	
	UNBALANCED	BALANCED
CHARACTERISTIC IMPEDANCE	100 Ω	168 Ω
CAPACITANCE	15.0 pF/ft [49.2 pF/m]	8.4 pF/ft [27.7 pF/m]
INDUCTANCE	0.15 μ H/ft [0.49 μ H/m]	0.24 μ H/ft [0.79 μ H/m]
PROPAGATION DELAY	1.51 ns/ft [4.95 ns/m]	1.42 ns/ft [4.66 ns/m]
VELOCITY OF PROPAGATION	68%	72%

NOTE: UNBALANCED IS MEASURED BETWEEN GROUND-SIGNAL-GROUND CONDUCTORS.
BALANCED IS MEASURED WITHIN A PAIR.

ROLLING FLEX CYCLES PER
EIA-364-41

RADIUS	MINIMUM CYCLES
1/2 ⁰⁰	0.4 MILLION
3/4 ⁰⁰	5 MILLION
1 3/4 ⁰⁰	10 MILLION


NOTE: REPRESENTS MINIMUM ROLLING FLEX CYCLES AT DATE OF PUBLICATION. ADDITIONAL TESTING IS ONGOING. CABLE CONSTRUCTION AND MATERIAL IS SIMILAR TO 3319 SERIES CABLE WHICH IS RATED TO 100 MILLION CYCLES AT 7/8" RADIUS. SEE TS-0732. CONTACT 3M FOR THE MOST UP-TO-DATE INFORMATION.

3M™ ELECTRONIC SOLUTIONS DIVISION
INTERCONNECT SOLUTIONS
<http://www.3mconnectors.com>

3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION CALL 800-225-5373

AWM 21682 105 °C 300V HOR  AWM 1A 105 ° 150V FT2 EU<50V



DESIGN REFERENCE NEXT ASSEMBLY		A 44734		DEC 06, 2012		JNC		RE	
REV ECO		ISSUE DATE AND DESCRIPTION CASTiglione		DATE NOV 05, 2012		MFG DATE		CHKD DATE	
DIVISION Interconnect Solutions		DIVISION CODE ISD		3M Center St. Paul, MN 55144		APPROV R EDWARDS		DATE NOV 05, 2012	
DO NOT SCALE DRAWING		TOLERANCES EXCEPT AS NOTED		3M 3M Center St. Paul, MN 55144		© 3M COPYRIGHT 2013 This document and the information it contains are 3M property and may not be reproduced or further distributed without the express permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.			
		INCHES .00 ± .01 .00 ± .05 .0000 ± .010		TITLE MEDIUM FLEX LIFE FLAT CABLE , .050" , 28 AWG , HF539					
THIRD ANGLE PROJECTION INTERPRET PER ASME Y14.5 - 1994		MILLIMETERS 0 ± .25 .00 ± 1.3 .00 ± .25 .000 ±		CAGE NUMBER D 78-5100-2565-9		SIZE DRAWING NO.		REV. A	
MAX SURFACE ROUGHNESS 125 μm SURFACES ☒ MARKED ONLY		ANGLES		MODEL		DET. LISTS ☐ YES ☒ NO SHT 1 OF 1			