

## QUAD FREQUENCY CRYSTAL OSCILLATOR (XO) (10 MHz TO 1.4 GHz)

### Features

- Available with any-rate output frequencies from 10 MHz to 945 MHz and select frequencies to 1.4 GHz
- Four selectable output frequencies
- 3rd generation DSPLL® with superior jitter performance
- 3x better frequency stability than SAW-based oscillators
- Internal fixed crystal frequency ensures high reliability and low aging
- Available CMOS, LVPECL, LVDS, and CML outputs
- 3.3, 2.5, and 1.8 V supply options
- Industry-standard 5 x 7 mm package and pinout
- Pb-free/RoHS-compliant


### Applications

- SONET/SDH
- Networking
- SD/HD video
- Test and measurement
- Clock and data recovery
- FPGA/ASIC clock generation

### Description

The Si534 quad frequency XO utilizes Silicon Laboratories' advanced DSPLL® circuitry to provide a low jitter clock at high frequencies. The Si534 is available with any-rate output frequency from 10 to 945 MHz and select frequencies to 1400 MHz. Unlike a traditional XO where a different crystal is required for each output frequency, the Si534 uses one fixed crystal to provide a wide range of output frequencies. This IC-based approach allows the crystal resonator to provide exceptional frequency stability and reliability. In addition, DSPLL clock synthesis provides superior supply noise rejection, simplifying the task of generating low jitter clocks in noisy environments typically found in communication systems. The Si534 IC-based XO is factory configurable for a wide variety of user specifications including frequency, supply voltage, output format, and temperature stability. Specific configurations are factory programmed at time of shipment, thereby eliminating long lead times associated with custom oscillators.

### Functional Block Diagram




### Ordering Information:

See page 7.


### Pin Assignments:

See page 6.

(Top View)



(LVDS/LVPECL/CML)



(CMOS)

## 1. Electrical Specifications

**Table 1. Recommended Operating Conditions**

| Parameter                                                                                                                                                                                                               | Symbol   | Test Condition           | Min                  | Typ | Max  | Units |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|--------------------------|----------------------|-----|------|-------|
| Supply Voltage <sup>1</sup>                                                                                                                                                                                             | $V_{DD}$ | 3.3 V option             | 2.97                 | 3.3 | 3.63 | V     |
|                                                                                                                                                                                                                         |          | 2.5 V option             | 2.25                 | 2.5 | 2.75 | V     |
|                                                                                                                                                                                                                         |          | 1.8 V option             | 1.71                 | 1.8 | 1.89 | V     |
| Supply Current                                                                                                                                                                                                          | $I_{DD}$ | Output enabled<br>LVPECL | —                    | 111 | 121  | mA    |
|                                                                                                                                                                                                                         |          | CML                      | —                    | 99  | 108  |       |
|                                                                                                                                                                                                                         |          | LVDS                     | —                    | 90  | 98   |       |
|                                                                                                                                                                                                                         |          | CMOS                     | —                    | 81  | 88   |       |
|                                                                                                                                                                                                                         |          | Tristate mode            | —                    | 60  | 75   | mA    |
| Output Enable (OE)<br>and Frequency Select FS[1:0] <sup>2</sup>                                                                                                                                                         |          | $V_{IH}$                 | $0.75 \times V_{DD}$ | —   | —    | V     |
|                                                                                                                                                                                                                         |          | $V_{IL}$                 | —                    | —   | 0.5  | V     |
| Operating Temperature Range                                                                                                                                                                                             | $T_A$    |                          | −40                  | —   | 85   | °C    |
| <b>Notes:</b><br>1. Selectable parameter specified by part number. See Section 3. "Ordering Information" on page 7 for further details.<br>2. OE and FS[1:0] pins include a 17 k $\Omega$ pullup resistor to $V_{DD}$ . |          |                          |                      |     |      |       |

**Table 2. CLK± Output Frequency Characteristics**

| Parameter                            | Symbol         | Test Condition                         | Min              | Typ         | Max              | Units |
|--------------------------------------|----------------|----------------------------------------|------------------|-------------|------------------|-------|
| Nominal Frequency <sup>1,2</sup>     | f <sub>O</sub> | LVPECL/LVDS/CML                        | 10               | —           | 945              | MHz   |
|                                      |                | CMOS                                   | 10               | —           | 160              | MHz   |
| Initial Accuracy                     | f <sub>i</sub> | Measured at +25 °C at time of shipping | —                | ±1.5        | —                | ppm   |
| Temperature Stability <sup>1,3</sup> |                |                                        | −7<br>−20<br>−50 | —<br>—<br>— | +7<br>+20<br>+50 | ppm   |
| Aging                                | f <sub>a</sub> | Frequency drift over first year        | —                | —           | ±3               | ppm   |
|                                      |                | Frequency drift over 20-year life      | —                | —           | ±10              | ppm   |
| Total Stability                      |                | Temp stability = ±7 ppm                | —                | —           | ±20              | ppm   |
|                                      |                | Temp stability = ±20 ppm               | —                | —           | ±31.5            | ppm   |
|                                      |                | Temp stability = ±50 ppm               | —                | —           | ±61.5            | ppm   |

Notes:

1.

See Section 3. "Ordering Information" on page 7 for further details.

2.

Specified at time of order by part number. Also available in frequencies from 970 to 1134 MHz and 1213 to 1417 MHz.

3.

Selectable parameter specified by part number.

4.

Time from powerup or tristate mode to f<sub>O</sub>.

Table 2. CLK± Output Frequency Characteristics (Continued)

| Parameter                                                                                                                                                                                                                                                                                                                                                                                              | Symbol    | Test Condition                               | Min | Typ | Max | Units |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|----------------------------------------------|-----|-----|-----|-------|
| Powerup Time <sup>4</sup>                                                                                                                                                                                                                                                                                                                                                                              | $t_{OSC}$ |                                              | —   | —   | 10  | ms    |
| Settling Time After FS[1:0] Change                                                                                                                                                                                                                                                                                                                                                                     | $t_{FRQ}$ | Both FS[1] and FS[0] changing simultaneously | —   | —   | 20  | ms    |
| <b>Notes:</b> <ol style="list-style-type: none"> <li>1. See Section 3. "Ordering Information" on page 7 for further details.</li> <li>2. Specified at time of order by part number. Also available in frequencies from 970 to 1134 MHz and 1213 to 1417 MHz.</li> <li>3. Selectable parameter specified by part number.</li> <li>4. Time from powerup or tristate mode to <math>f_O</math>.</li> </ol> |           |                                              |     |     |     |       |

Table 3. CLK± Output Levels and Symmetry

| Parameter                                                                                                                                                                                                                     | Symbol     | Test Condition                                                             | Min                 | Typ             | Max             | Units    |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|----------------------------------------------------------------------------|---------------------|-----------------|-----------------|----------|
| LVPECL Output Option <sup>1</sup>                                                                                                                                                                                             | $V_O$      | mid-level                                                                  | $V_{DD} - 1.42$     | —               | $V_{DD} - 1.25$ | V        |
|                                                                                                                                                                                                                               | $V_{OD}$   | swing (diff)                                                               | 1.1                 | —               | 1.9             | $V_{PP}$ |
|                                                                                                                                                                                                                               | $V_{SE}$   | swing (single-ended)                                                       | 0.55                | —               | 0.95            | $V_{PP}$ |
| LVDS Output Option <sup>2</sup>                                                                                                                                                                                               | $V_O$      | mid-level                                                                  | 1.125               | 1.20            | 1.275           | V        |
|                                                                                                                                                                                                                               | $V_{OD}$   | swing (diff)                                                               | 0.5                 | 0.7             | 0.9             | $V_{PP}$ |
| CML Output Option <sup>2</sup>                                                                                                                                                                                                | $V_O$      | 2.5/3.3 V option mid-level                                                 | —                   | $V_{DD} - 1.30$ | —               | V        |
|                                                                                                                                                                                                                               |            | 1.8 V option mid-level                                                     | —                   | $V_{DD} - 0.36$ | —               | V        |
|                                                                                                                                                                                                                               | $V_{OD}$   | 2.5/3.3 V option swing (diff)                                              | 1.10                | 1.50            | 1.90            | $V_{PP}$ |
|                                                                                                                                                                                                                               |            | 1.8 V option swing (diff)                                                  | 0.35                | 0.425           | 0.50            | $V_{PP}$ |
| CMOS Output Option <sup>3</sup>                                                                                                                                                                                               | $V_{OH}$   | $I_{OH} = 32$ mA                                                           | $0.8 \times V_{DD}$ | —               | $V_{DD}$        | V        |
|                                                                                                                                                                                                                               | $V_{OL}$   | $I_{OL} = 32$ mA                                                           | —                   | —               | 0.4             | V        |
| Rise/Fall time (20/80%)                                                                                                                                                                                                       | $t_R, t_F$ | LVPECL/LVDS/CML                                                            | —                   | —               | 350             | ps       |
|                                                                                                                                                                                                                               |            | CMOS with $C_L = 15$ pF                                                    | —                   | 1               | —               | ns       |
| Symmetry (duty cycle)                                                                                                                                                                                                         | SYM        | LVPECL: $V_{DD} - 1.3$ V (diff)<br>LVDS: 1.25 V (diff)<br>CMOS: $V_{DD}/2$ | 45                  | —               | 55              | %        |
| <b>Notes:</b> <ol style="list-style-type: none"> <li>1. <math>50 \Omega</math> to <math>V_{DD} - 2.0</math> V.</li> <li>2. <math>R_{term} = 100 \Omega</math> (differential).</li> <li>3. <math>C_L = 15</math> pF</li> </ol> |            |                                                                            |                     |                 |                 |          |

Table 4. CLK± Output Phase Jitter

| Parameter                                                                                                                                                                                                                       | Symbol         | Test Condition                         | Min | Typ  | Max  | Units |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|----------------------------------------|-----|------|------|-------|
| Phase Jitter (RMS) <sup>1</sup><br>for F <sub>OUT</sub> ≥ 500 MHz                                                                                                                                                               | ϕ <sub>J</sub> | 12 kHz to 20 MHz (OC-48)               | —   | 0.25 | 0.40 | ps    |
|                                                                                                                                                                                                                                 |                | 50 kHz to 80 MHz (OC-192)              | —   | 0.26 | 0.37 | ps    |
| Phase Jitter (RMS) <sup>1</sup><br>for F <sub>OUT</sub> of 125 to 500 MHz                                                                                                                                                       | ϕ <sub>J</sub> | 12 kHz to 20 MHz (OC-48)               | —   | 0.36 | 0.50 | ps    |
|                                                                                                                                                                                                                                 |                | 50 kHz to 80 MHz (OC-192) <sup>2</sup> | —   | 0.34 | 0.42 | ps    |
| Phase Jitter (RMS)<br>for F <sub>OUT</sub> of 10 to 160 MHz<br>CMOS Output Only                                                                                                                                                 | ϕ <sub>J</sub> | 12 kHz to 20 MHz (OC-48) <sup>2</sup>  | —   | 0.62 | —    | ps    |
|                                                                                                                                                                                                                                 |                | 50 kHz to 20 MHz <sup>2</sup>          | —   | 0.61 | —    | ps    |
| <b>Notes:</b><br>1. Refer to AN256 for further information.<br>2. Max offset frequencies: 80 MHz for F <sub>OUT</sub> ≥ 250 MHz, 20 MHz for 50 MHz ≤ F <sub>OUT</sub> <250 MHz,<br>2 MHz for 10 MHz ≤ F <sub>OUT</sub> <50 MHz. |                |                                        |     |      |      |       |

Table 5. CLK± Output Period Jitter

| Parameter                                                                                                           | Symbol           | Test Condition | Min | Typ | Max | Units |
|---------------------------------------------------------------------------------------------------------------------|------------------|----------------|-----|-----|-----|-------|
| Period Jitter*                                                                                                      | J <sub>PER</sub> | RMS            | —   | 2   | —   | ps    |
|                                                                                                                     |                  | Peak-to-Peak   | —   | 14  | —   | ps    |
| *Note: Any output mode, including CMOS, LVPECL, LVDS, CML. N = 1000 cycles. Refer to AN279 for further information. |                  |                |     |     |     |       |

Table 6. CLK± Output Phase Noise (Typical)

| Offset Frequency (f) | 120.00 MHz<br>LVDS | 156.25 MHz<br>LVPECL | 622.08 MHz<br>LVPECL | Units  |
|----------------------|--------------------|----------------------|----------------------|--------|
| 100 Hz               | −112               | −105                 | −97                  | dBc/Hz |
| 1 kHz                | −122               | −122                 | −107                 |        |
| 10 kHz               | −132               | −128                 | −116                 |        |
| 100 kHz              | −137               | −135                 | −121                 |        |
| 1 MHz                | −144               | −144                 | −134                 |        |
| 10 MHz               | −150               | −147                 | −146                 |        |
| 100 MHz              | n/a                | n/a                  | −148                 |        |

**Table 7. Environmental Compliance**

The Si534 meets the following qualification test requirements.

| Parameter                  | Conditions/Test Method   |
|----------------------------|--------------------------|
| Mechanical Shock           | MIL-STD-883, Method 2002 |
| Mechanical Vibration       | MIL-STD-883, Method 2007 |
| Solderability              | MIL-STD-883, Method 2003 |
| Gross & Fine Leak          | MIL-STD-883, Method 1014 |
| Resistance to Solder Heat  | MIL-STD-883, Method 2036 |
| Moisture Sensitivity Level | J-STD_020, MSL1          |
| Contact Pads               | Gold over Nickel         |

**Table 8. Thermal Characteristics**

(Typical values  $T_A = 25\text{ }^{\circ}\text{C}$ ,  $V_{DD} = 3.3\text{ V}$ )

| Parameter                              | Symbol        | Test Condition | Min | Typ  | Max | Unit                 |
|----------------------------------------|---------------|----------------|-----|------|-----|----------------------|
| Thermal Resistance Junction to Ambient | $\theta_{JA}$ | Still Air      | —   | 84.6 | —   | $^{\circ}\text{C/W}$ |
| Thermal Resistance Junction to Case    | $\theta_{JC}$ | Still Air      | —   | 38.8 | —   | $^{\circ}\text{C/W}$ |
| Ambient Temperature                    | $T_A$         |                | −40 | —    | 85  | $^{\circ}\text{C}$   |
| Junction Temperature                   | $T_J$         |                | —   | —    | 125 | $^{\circ}\text{C}$   |

**Table 9. Absolute Maximum Ratings<sup>1</sup>**


| Parameter                                                              | Symbol     | Rating                 | Units              |
|------------------------------------------------------------------------|------------|------------------------|--------------------|
| Maximum Operating Temperature                                          | $T_{AMAX}$ | 85                     | $^{\circ}\text{C}$ |
| Supply Voltage, 1.8 V Option                                           | $V_{DD}$   | −0.5 to +1.9           | V                  |
| Supply Voltage, 2.5/3.3 V Option                                       | $V_{DD}$   | −0.5 to +3.8           | V                  |
| Input Voltage (any input pin)                                          | $V_I$      | −0.5 to $V_{DD} + 0.3$ | V                  |
| Storage Temperature                                                    | $T_S$      | −55 to +125            | $^{\circ}\text{C}$ |
| ESD Sensitivity (HBM, per JESD22-A114)                                 | ESD        | 2000                   | V                  |
| Soldering Temperature (Pb-free profile) <sup>2</sup>                   | $T_{PEAK}$ | 260                    | $^{\circ}\text{C}$ |
| Soldering Temperature Time @ $T_{PEAK}$ (Pb-free profile) <sup>2</sup> | $t_P$      | 20–40                  | seconds            |

**Notes:**


1. Stresses beyond those listed in Absolute Maximum Ratings may cause permanent damage to the device. Functional operation or specification compliance is not implied at these conditions. Exposure to maximum rating conditions for extended periods may affect device reliability.
2. The device is compliant with JEDEC J-STD-020C. Refer to Si5xx Packaging FAQ available for download at [www.silabs.com/VCXO](http://www.silabs.com/VCXO) for further information, including soldering profiles.

## 2. Pin Descriptions

(Top View)



**LVDS/LVPECL/CML**



**CMOS**

**Table 10. Pin Descriptions**

| Pin                                                                                                                                                                        | Symbol          | LVDS/LVPECL/CML Function                                                                   | CMOS Function                                                                              |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|--------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| 1                                                                                                                                                                          | NC              | No connection                                                                              | No connection                                                                              |
| 2                                                                                                                                                                          | OE*             | Output enable<br>0 = clock output disabled (outputs tristated)<br>1 = clock output enabled | Output enable<br>0 = clock output disabled (outputs tristated)<br>1 = clock output enabled |
| 3                                                                                                                                                                          | GND             | Electrical and Case Ground                                                                 | Electrical and Case Ground                                                                 |
| 4                                                                                                                                                                          | CLK+            | Oscillator Output                                                                          | Oscillator Output                                                                          |
| 5                                                                                                                                                                          | CLK–            | Complementary Output                                                                       | No connection                                                                              |
| 6                                                                                                                                                                          | V <sub>DD</sub> | Power Supply Voltage                                                                       | Power Supply Voltage                                                                       |
| 7                                                                                                                                                                          | FS[1]*          | Frequency Select MSB                                                                       | Frequency Select MSB                                                                       |
| 8                                                                                                                                                                          | FS[0]*          | Frequency Select LSB                                                                       | Frequency Select LSB                                                                       |
| <b>*Note:</b> FS[1:0] and OE include a 17 kΩ pullup resistor to V <sub>DD</sub> . See Section 3. "Ordering Information" on page 7 for details on frequency value ordering. |                 |                                                                                            |                                                                                            |

### 3. Ordering Information

The Si534 XO supports a variety of options including frequency, temperature stability, output format, and  $V_{DD}$ . Specific device configurations are programmed into the Si534 at time of shipment. Configurations can be specified using the Part Number Configuration chart below. Silicon Laboratories provides a web browser-based part number configuration utility to simplify this process. Refer to [www.silabs.com/VCXOPartNumber](http://www.silabs.com/VCXOPartNumber) to access this tool and for further ordering instructions. The Si534 is supplied in an industry-standard, RoHS compliant, 6-pad, 5 x 7 mm package.





Figure 1. Part Number Convention

## 4. Outline Diagram and Suggested Pad Layout

Figure 2 illustrates the package details for the Si534. Table 11 lists the values for the dimensions shown in the illustration.



**Figure 2. Si534 Outline Diagram**

**Table 11. Package Diagram Dimensions (mm)**


| Dimension | Min      | Nom  | Max  |
|-----------|----------|------|------|
| A         | 1.50     | 1.65 | 1.80 |
| b         | 1.30     | 1.40 | 1.50 |
| b1        | 0.90     | 1.00 | 1.10 |
| c         | 0.50     | 0.60 | 0.70 |
| c1        | 0.30     | —    | 0.60 |
| D         | 5.00 BSC |      |      |
| D1        | 4.30     | 4.40 | 4.50 |
| e         | 2.54 BSC |      |      |
| E         | 7.00 BSC |      |      |
| E1        | 6.10     | 6.20 | 6.30 |
| H         | 0.55     | 0.65 | 0.75 |
| L         | 1.17     | 1.27 | 1.37 |
| L1        | 1.07     | 1.17 | 1.27 |
| p         | 1.80     | —    | 2.60 |
| R         | 0.70 REF |      |      |
| aaa       | —        | —    | 0.15 |
| bbb       | —        | —    | 0.15 |
| ccc       | —        | —    | 0.10 |
| ddd       | —        | —    | 0.10 |
| eee       | —        | —    | 0.05 |

**Note:**

1. All dimensions shown are in millimeters (mm) unless otherwise noted.
2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.

## 5. Si534 Mark Specification

Figure 3 illustrates the mark specification for the Si534. Table 12 lists the line information.




**Figure 3. Mark Specification**

**Table 12. Si53x Top Mark Description**

| Line | Position          | Description                                                                                                                                            |
|------|-------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| 1    | 1–10              | “SiLabs 534”                                                                                                                                           |
| 2    | 1–10              | Si530, Si531: Option1 + Option2 + Freq(7) + Temp<br>Si532, Si533, Si534, Si530/Si531 w/ 8-digit resolution:<br>Option1 + Option2 + ConfigNum(6) + Temp |
| 3    | <b>Trace Code</b> |                                                                                                                                                        |
|      | Position 1        | Pin 1 orientation mark (dot)                                                                                                                           |
|      | Position 2        | Product Revision (D)                                                                                                                                   |
|      | Position 3–6      | Tiny Trace Code (4 alphanumeric characters per assembly release instructions)                                                                          |
|      | Position 7        | Year (least significant year digit), to be assigned by assembly site (ex: 2007 = 7)                                                                    |
|      | Position 8–9      | Calendar Work Week number (1–53), to be assigned by assembly site                                                                                      |
|      | Position 10       | “+” to indicate Pb-Free and RoHS-compliant                                                                                                             |

## 6. 8-Pin PCB Land Pattern

Figure 4 illustrates the 8-pin PCB land pattern for the Si554. Table 13 lists the values for the dimensions shown in the illustration.



**Figure 4. Si534 PCB Land Pattern**

**Table 13. PCB Land Pattern Dimensions (mm)**

| Dimension | Min       | Max  |
|-----------|-----------|------|
| D2        | 5.08 REF  |      |
| D3        | 5.705 REF |      |
| e         | 2.54 BSC  |      |
| E2        | 4.20 REF  |      |
| GD        | 0.84      | —    |
| GE        | 2.00      | —    |
| VD        | 8.20 REF  |      |
| VE        | 7.30 REF  |      |
| X1        | 1.70 TYP  |      |
| X2        | 1.545 TYP |      |
| Y1        | 2.15 REF  |      |
| Y2        | 1.3 REF   |      |
| ZD        | —         | 6.78 |
| ZE        | —         | 6.30 |

**Note:**

1. Dimensioning and tolerancing per the ANSI Y14.5M-1994 specification.
2. Land pattern design follows IPC-7351 guidelines.
3. All dimensions shown are at maximum material condition (MMC).
4. Controlling dimension is in millimeters (mm).

## DOCUMENT CHANGE LIST

### Revision 1.0 to Revision 1.1

- Updated Table 1, "Recommended Operating Conditions," on page 2.
  - Device maintains stable operation over  $-40$  to  $+85$  °C operating temperature range.
  - Supply current specifications updated for revision D.
- Updated Table 2, "CLK± Output Frequency Characteristics," on page 2.
  - Added specification for  $\pm 20$  ppm lifetime stability ( $\pm 7$  ppm temperature stability) XO.
- Updated Table 3, "CLK± Output Levels and Symmetry," on page 3.
  - Updated LVDS differential peak-peak swing specifications.
- Updated Table 4, "CLK± Output Phase Jitter," on page 4.
- Updated Table 5, "CLK± Output Period Jitter," on page 4.
  - Revised period jitter specifications.
- Updated Table 9, "Absolute Maximum Ratings<sup>1</sup>," on page 5 to reflect the soldering temperature time at  $260$  °C is 20–40 sec per JEDEC J-STD-020C.
- Updated 3. "Ordering Information" on page 7.
  - Changed ordering instructions to revision D.
- Added 5. "Si534 Mark Specification" on page 9.

### Revision 1.1 to Revision 1.2

- Updated 2.5 V/3.3 V and 1.8 V CML output level specifications for Table 3 on page 3.
- Added footnotes clarifying max offset frequency test conditions for Table 4 on page 4.
- Removed the words "Differential Modes: LVPECL/LVDS/CML" in the footnote referring to AN256 in Table 4 on page 4.
- Added CMOS phase jitter specs to Table 4 on page 4.
- Updated ESD HBM sensitivity rating in Table 9 on page 5.
- Updated Table 7 on page 5 to include the "Moisture Sensitivity Level" and "Contact Pads" rows.
- Revised Figure 2 on page 8 to reflect current package outline diagram.
- Updated Figure 3 and Table 12 on page 9 to reflect specific marking information. Previously, Figure 3 was generic.

### Revision 1.2 to Revision 1.3

- Added Table 8, "Thermal Characteristics," on page 5.

## CONTACT INFORMATION

### Silicon Laboratories Inc.

400 West Cesar Chavez  
Austin, TX 78701  
Tel: 1+(512) 416-8500  
Fax: 1+(512) 416-9669  
Toll Free: 1+(877) 444-3032

Please visit the Silicon Labs Technical Support web page:

<https://www.silabs.com/support/pages/contacttechnicalsupport.aspx>

and register to submit a technical support request.

The information in this document is believed to be accurate in all respects at the time of publication but is subject to change without notice. Silicon Laboratories assumes no responsibility for errors and omissions, and disclaims responsibility for any consequences resulting from the use of information included herein. Additionally, Silicon Laboratories assumes no responsibility for the functioning of undescribed features or parameters. Silicon Laboratories reserves the right to make changes without further notice. Silicon Laboratories makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Silicon Laboratories assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Silicon Laboratories products are not designed, intended, or authorized for use in applications intended to support or sustain life, or for any other application in which the failure of the Silicon Laboratories product could create a situation where personal injury or death may occur. Should Buyer purchase or use Silicon Laboratories products for any such unintended or unauthorized application, Buyer shall indemnify and hold Silicon Laboratories harmless against all claims and damages.

Silicon Laboratories, Silicon Labs, and DSPLL are trademarks of Silicon Laboratories Inc.

Other products or brandnames mentioned herein are trademarks or registered trademarks of their respective holders.