

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [30700-1102](#)
Status: **Active**
Overview: H-DAC 64™ Dual-Row High Density Automotive Connectors
Description: 2.54mm Pitch, 0.64mm Width H-DAC 64™ High Density Automotive Connectors, Dual Row, Female Harness Assembly, 10 Circuits, Polarization Option 3, Natural

Documents:

3D Model	Product Specification PS-34646-001 (PDF)
Drawing (PDF)	Application Specification AS-30700-000 (PDF)
Product Specification PS-30700-0001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-30968-0001 (PDF)	

General

Product Family	Crimp Housings
Series	30700
Application	Power, Wire-to-Wire
Comments	Polarization Option 3
Overview	H-DAC 64™ Dual-Row High Density Automotive Connectors
Product Name	H-DAC 64™
UPC	800756075020

Physical

Circuits (maximum)	10
Color - Resin	Natural
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene
Net Weight	3.330/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

Current - Maximum per Contact	7A
-------------------------------	----

Material Info

Reference - Drawing Numbers

Application Specification	AS-30700-000
Product Specification	PS-30700-0001, PS-30968-0001, PS-34646-001
Sales Drawing	SD-30700-120



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[30700Series](#)

Mates With
[30700](#) Header, [30968](#) Crimp Housing

Use With
[34230](#) Terminal

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

30700-1102