


2,500 V - 10,000 V Rectifiers

0.50 A - 1.5 A Forward Current
200 ns Recovery Time

Z25FG
Z50FG
Z100FG


AXIAL LEADED
HERMETICALLY SEALED



4

ELECTRICAL CHARACTERISTICS AND MAXIMUM RATINGS

Part Number	Working Reverse Voltage	Average Rectified Current		Reverse Current @ Vrwm		Forward Voltage		1 Cycle Surge Current tp=8.3ms (Ifsm)	Repetitive Surge Current (Ifrm)	Reverse Recovery Time (3) (Trr)	Thermal Impedance			Junction Cap. @50VDC @ 1kHz (Cj)
	(Vrwm)	(Io)		(Ir)		(Vf)					θ_{J-L}			
		55°C(1)	100°C(2)	25°C	100°C	25°C		25°C	25°C	25°C	L=000	L=.125	L=.250	25°C
	Volts	Amps	Amps	µA	µA	Volts	Amps	Amps	Amps	Amps	ns	°C/W	°C/W	°C/W
Z25FG	2500	1.50	1.00	1.0	25	6.5	2.00	60	10	200	3	6	12	20
Z50FG	5000	1.00	0.50	1.0	25	9.5	1.00	40	8	200	3	6	12	16
Z100FG	10000	0.50	0.25	1.0	25	13.0	0.60	25	5	200	3	6	12	8
(1)TL=55°C L=0.375" (2)TL=100°C L=0.375" (3)If=0.5A, Ir=1.0A, Irr=0.25A • Op.Temp.= -65°C to +175°C Stg.Temp.= -65°C to +200°C														



Part	A
Z25FG Z50FG	.350(8.89) MAX.
Z100FG	.400(10.16) MAX.



Dimensions: In. (mm) • All temperatures are ambient unless otherwise noted. • Data subject to change without notice.



VOLTAGE MULTIPLIERS INC.
8711 W. Roosevelt Ave.
Visalia, CA 93291

TEL 559-651-1402
FAX 559-651-0740
www.voltagemultipliers.com

Z25FG Z50FG Z100FG

