


2278896
THIS DRAWING IS A CONTROLLED DOCUMENT

Restricted to: General Release

USED ON




Left Side

Connector(s): MT-RJ SECURE (No Pins)

Mode: MM

Housing Color: Green

Geom. Spec: 115-1215



VIEW C-C
NOT TO SCALE

Fiber Path

Fiber A - ——— - B
Fiber B - ——— - A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Label 2 will not be present on any cable assembly less than 5 meters long.
- 3 Includes dust caps (not shown on print).
- 4 IL tested at 1300nm.

Right Side

Connector(s): SC-Duplex

Mode: MM


Housing Color: Beige

Geom. Spec: N/A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

	B	Rev Per EC#	06-021324	9/14/2006	-	MK			
P	LTR	REVISION	RECORD	DATE	DN	APVD			



DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
meters	
0 P.L.C.	± .
1 P.L.C.	± .
2 P.L.C.	± .
3 P.L.C.	± .
4 P.L.C.	± .

Customer Print

DN	Cable Assy Configurator	MATERIAL	HEAT TREAT
OK	Michael Kepko		
APVD	Michael Kepko		
NAME	FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex		
SCALE	SIZE	DRAWING NO	SHEET
NTS	A2	C- 6278896	1 of 3
			REV B

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Restricted to: General Release

USED ON

THIS DRAWING IS A CONTROLLED DOCUMENT.

Part #	L (meters)	L (feet)	MT-RJ SECURE (No Pins), Green		SC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-6278896-1	0.950 - 1.050	3.11 - 3.44	0.5	20	0.5	-
0-6278896-2	1.950 - 2.050	6.39 - 6.72	0.5	20	0.5	-
0-6278896-3	2.950 - 3.050	9.67 - 10.00	0.5	20	0.5	-
0-6278896-4	3.920 - 4.080	12.86 - 13.38	0.51	20	0.51	-
0-6278896-5	4.920 - 5.080	16.14 - 16.66	0.51	20	0.51	-
0-6278896-6	5.920 - 6.080	19.42 - 19.94	0.51	20	0.51	-
0-6278896-7	6.920 - 7.080	22.70 - 23.22	0.51	20	0.51	-
0-6278896-8	7.920 - 8.080	25.98 - 26.50	0.51	20	0.51	-
0-6278896-9	8.850 - 9.150	29.03 - 30.01	0.51	20	0.51	-
1-6278896-0	9.850 - 10.150	32.31 - 33.30	0.52	20	0.52	-
1-6278896-1	10.850 - 11.150	35.59 - 36.58	0.52	20	0.52	-
1-6278896-2	11.850 - 12.150	38.87 - 39.86	0.52	20	0.52	-
1-6278896-3	12.850 - 13.150	42.15 - 43.14	0.52	20	0.52	-
1-6278896-4	13.850 - 14.150	45.43 - 46.42	0.52	20	0.52	-
1-6278896-5	14.850 - 15.150	48.72 - 49.70	0.52	20	0.52	-
1-6278896-6	15.840 - 16.160	51.96 - 53.01	0.52	20	0.52	-
1-6278896-7	16.830 - 17.170	55.21 - 56.33	0.53	20	0.53	-
1-6278896-8	17.820 - 18.180	58.46 - 59.64	0.53	20	0.53	-
1-6278896-9	18.810 - 19.190	61.71 - 62.95	0.53	20	0.53	-
2-6278896-0	19.800 - 20.200	64.96 - 66.27	0.53	20	0.53	-
2-6278896-1	20.790 - 21.210	68.20 - 69.58	0.53	20	0.53	-
2-6278896-2	21.780 - 22.220	71.45 - 72.90	0.53	20	0.53	-
2-6278896-3	22.770 - 23.230	74.70 - 76.21	0.53	20	0.53	-
2-6278896-4	23.760 - 24.240	77.95 - 79.52	0.54	20	0.54	-
2-6278896-5	24.750 - 25.250	81.20 - 82.84	0.54	20	0.54	-
2-6278896-6	25.740 - 26.260	84.44 - 86.15	0.54	20	0.54	-
2-6278896-7	26.730 - 27.270	87.69 - 89.46	0.54	20	0.54	-
2-6278896-8	27.720 - 28.280	90.94 - 92.78	0.54	20	0.54	-
2-6278896-9	28.710 - 29.290	94.19 - 96.09	0.54	20	0.54	-
3-6278896-0	29.700 - 30.300	97.44 - 99.40	0.55	20	0.55	-
3-6278896-1	30.690 - 31.310	100.68 - 102.72	0.55	20	0.55	-
3-6278896-2	31.680 - 32.320	103.93 - 106.03	0.55	20	0.55	-
3-6278896-3	32.670 - 33.330	107.18 - 109.35	0.55	20	0.55	-
3-6278896-4	33.660 - 34.340	110.43 - 112.66	0.55	20	0.55	-
3-6278896-5	34.650 - 35.350	113.68 - 115.97	0.55	20	0.55	-
3-6278896-6	35.640 - 36.360	116.92 - 119.29	0.55	20	0.55	-
3-6278896-7	36.630 - 37.370	120.17 - 122.60	0.56	20	0.56	-
3-6278896-8	37.620 - 38.380	123.42 - 125.91	0.56	20	0.56	-
3-6278896-9	38.610 - 39.390	126.67 - 129.23	0.56	20	0.56	-
4-6278896-0	39.600 - 40.400	129.92 - 132.54	0.56	20	0.56	-
5-6278896-0	49.500 - 50.500	162.40 - 165.68	0.58	20	0.58	-
9-6278896-0	106.673 - 108.828	349.97 - 357.04	0.66	20	0.66	-

Qty	U of M	Description	Item No.
1	piece	DUST COVER, MT-RJ	1
1	piece	SPRING, MT-RJ, 3.8 DESIGN	2
1	piece	PIN KEEPER, 3.8MM	3
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	4
1	piece	CRIMP EYELET, MT-RJ	5
1	piece	MT-RJ Keyed Connector Housing - Green	6
2	piece	LC, SC, FC Straight Boot, Beige	7
1	piece	MT-RJ FERRULE, THERMOPLAST,MM	8
2	piece	SC Simplex Housing, Beige	9
2	piece	2.5mm ferrule cover	10
AR	meter	2 fiber, 62.5/125, 1.8 mm, Twinzip, Orange, OFNR (Riser)	11
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	12
2	piece	SC Duplex Clip	13
2	piece	Eyelet/Shrink tube assembly - White	14
2	piece	CONN SUBASSY, MM, SC 1.6MM	15
2	piece	Trace Label	16

B	Rev Per EC#	06-021324	9/14/2006	-	MK
P	LTR	REVISION RECORD	DATE	DIN	APVD

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 P.L.C. ±
1 P.L.C. ±
2 P.L.C. ±
3 P.L.C. ±
4 P.L.C. ±

Customer Print

DIN	Cable Assy Configurator	MATERIAL	-	HEAT TREAT	-
OK	Michael Kepko	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD	Michael Kepko				
NAME	FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex				
SCALE	NTS	SIZE	A2	DRAWING NO	C- 6278896
SHEET	2 of 3	REV	B		

8 7 6 5 4 3 2 1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

THIS DRAWING IS A CONTROLLED DOCUMENT.
PAGE NO

Restricted to: General Release

Part #	L (meters)	L (feet)	MT-RJ SECURE (No Pins), Green		SC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
9-6278896-1	121.909 - 124.371	399.96 - 408.04	0.69	20	0.69	-
9-6278896-2	152.386 - 155.464	499.95 - 510.05	0.73	20	0.73	-

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

B	Rev Per EC#	06-021324	9/14/2006	-	MK		
P	LTR	REVISION RECORD	DATE	DIN	APVD		

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
meters		9 P.L.C.	± .
		1 P.L.C.	± .
		2 P.L.C.	± .
		3 P.L.C.	± .
		4 P.L.C.	± .

DIN		Cable Assy Configurator		MATERIAL	HEAT TREAT				
OK		Michael Kepko							
APVD		Michael Kepko							
NAME FO C/A - 2 fiber, 62.5/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex									
SCALE	NTS	SIZE	A2	DRAWING NO	C- 6278896	SHEET	3 of 3	REV	B

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1