



LOC	DIST	REVISIONS					
G	86	P	LTR	DESCRIPTION	DATE	DWN	APVD
			M	REL PER 0G3A-0196-03	28MAR03	JR	MS

D



C

B



A

- 1 WIRE INSULATION:
END 'A' 13.21[.520] - 16.38[.645] DIA FOR 3/0 AL
END 'B' 10.92[.430] - 12.57[.495] DIA FOR 1/0 CU

2 STAMP " 277168-1 AMP 3/0AL-1/0CU"
APPROX AS SHOWN,

INSERT & FUNNEL: BRASS MIL-C-50 NICKEL PL QQ-N-290 0.00762[.000300] AVG THK SPLICE: COPPER ASTM B-187 TIN PL PER ASTM B-545 0.00381[.000150] MIN THK	277168-1
MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 7/5/89	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK MS FEHER 5/1/91		
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD MJ SPICER 5/1/91	NAME WIRE SPLICE, TRANSITIONAL, COPALUM	
	FINISH SEE TABLE	PRODUCT SPEC 108-11011 APPLICATION SPEC 114-2134	SIZE A2	CAGE CODE 00779
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT 128.5 GRAMS	DRAWING NO C=277168	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	REV M