



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
E	B		BA1	REVISED PER ECO-11-005150		29MAR2011	HMR


SERIES 3650-1J, 3650-2A AS SHOWN




- 1
- 2
- 3
- TERMINAL WRAPAROUND APPROX 0.007'' (0.18mm) BOTH ENDS
- AVAILABLE IN 2 DIFFERENT SERIES
- FOR FURTHER INFORMATION SEE DATA SHEET FOR 3650 SERIES-LOW INDUCTANCE, HIGH FREQUENCY CHIP INDUCTOR

RoHS Compliant


RECOMMENDED LAND PATTERN FOR 3650-2A, 3650-1J SERIES



3650-1J SERIES



3650-2A SERIES



3650-1J	1.80	1.12	1.02	0.38	0.76	0.33	0.86	1.02	0.64	0.64
3650-2A	2.29	1.73	1.52	0.51	1.27	0.51	1.02	1.78	1.02	0.76
SERIES	A Max.	B Max.	C Max.	D ref	E	F	G	H	K	J

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		
	0 PLC	± 0.2
	1 PLC	± 0.1
	2 PLC	± -
	3 PLC	± -
	4 PLC	± -
ANGLES		± 5°
MATERIAL	FINISH	-

DWN	SUBHASH.M	03-AUG-09
CHK	ALLAN.P	03-AUG-09
APVD	STEPHEN.P	03-AUG-09
PRODUCT SPEC		
APPLICATION SPEC		
WEIGHT		

STE TE Connectivity

LOW INDUCTANCE,
HIGH FREQUENCY CHIP
INDUCTOR SERIES 3650

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	1624113	-
CUSTOMER DRAWING			SCALE NTS
			SHEET 1 OF 1
			REV BA1