


1

2


3

4

5



Tolerance of Cutting Tilt



TOLERANCE:

Abbr.	TOLERANCE	
	P=0.5	P=1.0
P	±0.05	±0.08
Pt	±0.08	±0.10
W	±0.08	±0.10
M	±0.08	±0.12
Cw	±0.02	±0.03
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm	

No. of PIN	Dimension												
	P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0	d2±2.0	Ft±0.01	St±0.01
XX	0.5	(XX - 1 x P)	LLL	(XX + 1 x P)	0.5	0.3	0.05	4.0	4.0	8.0	8.0	0.043	0.225

TECHNICAL CHARACTERISTICS

MATERIAL

INSULATOR MATERIAL: PET (WHITE)
SUPPORT TAPE: PET (BLUE)
CONTACT MATERIAL: COPPER
CONTACT PLATING: TIN
QUALITY CLASS: 20 MATING CYCLES MIN.
PITCH: 0.50 MM

ENVIRONMENTAL

OPERATING TEMPERATURE: -30°C UP TO 105°C
HEAT RESISTANCE: 110°C x 96 HRS
FLAMMABILITY RATING UL SUB.758
MOISTURE RESISTANCE: 40°C, 95% RH x 96 HRS
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

CURRENT RATING: 0.5 A MAX
WORKING VOLTAGE: 60V
INSULATION RESISTANCE: >1000 MOHM/M (500 VDC)
DIELECTRIC STRENGTH: 500 VAC/MN NO BREAKDOWN
CONDUCTOR RESISTANCE: <1,40 OHM/M
CONTACT RESISTANCE: <20 MOHMS

STANDARD

CERTIFIED: E328849

MECHANICAL

ELONGATION OF INSULATOR: > 60 %
TENSILE STRENGTH OF INSULATION: >3.5KG/MM²
FLEXING TEST: 180° >20 TIMES
ABRASION: >10000 TIMES
PULL/OUT: >20 TIMES

PACKAGING

BAG

DIMENSION & TOLERANCE

W= (N+1) x P
Pt=(N-1) x P

RoHS Compliant

PROJECTION:



GENERAL TOLERANCE

.X = +/_ 0.2

.XX = +/_ 0.15



APPROVAL: GMo

UNIT: MM

SCALE:

SHEET: 1/2

DRAW: CH

DESCRIPTION: 0.50MM FLAT FLEXIBLE CABLE TYPE 2

XX NB OF PIN: / LLL OVERALL LENGTH: MM

WERI PART NO: 687 7 002

XX L L L

SIZE

A4

1				2				3				4				5				
Cautions and Warnings: This electronic component is designed and developed with the intention for use in general electronics equipments. Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Würth Elektronik must be asked for a written approval. In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.																	A			
																	B			
																	C			
																	D			
RoHS Compliant								PROJECTION:				GENERAL TOLERANCE								
G								.X = +/- 0.2 .XX = +/- 0.15												
F																				
E																				
D																				
C				APPROVAL: JC				UNIT: MM				DESCRIPTION: DISCLAIMER				SIZE				
B								SCALE:				WERI PART NO: DISCLAIMER				A4				
A	10-SEP-14	PDF	QL																	
REV	DATE	FILE	BY																	
								DRAW: QL												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Würth Electronics:

<u>687750200002</u>	<u>687708200002</u>	<u>687712200002</u>	<u>687720050002</u>	<u>687740050002</u>	<u>687724050002</u>	<u>687712050002</u>
<u>687730200002</u>	<u>687714200002</u>	<u>687718050002</u>	<u>687718200002</u>	<u>687710200002</u>	<u>687708050002</u>	<u>687750050002</u>
<u>687706050002</u>	<u>687720200002</u>	<u>687724200002</u>	<u>687716200002</u>	<u>687706200002</u>	<u>687730050002</u>	<u>687714050002</u>
<u>687716050002</u>	<u>687710050002</u>	<u>687740200002</u>	<u>687744100002</u>	<u>687732152002</u>	<u>687716152002</u>	<u>687724100002</u>
<u>687733152002</u>	<u>687726152002</u>	<u>687717100002</u>	<u>687726100002</u>	<u>687735100002</u>	<u>687706100002</u>	<u>687714100002</u>
<u>687722152002</u>	<u>687724152002</u>	<u>687728152002</u>	<u>687745152002</u>	<u>687708152002</u>	<u>687720152002</u>	<u>687740152002</u>
<u>687710152002</u>	<u>687714152002</u>	<u>687730152002</u>	<u>687744152002</u>	<u>687722100002</u>	<u>687750152002</u>	<u>687735152002</u>
<u>687712152002</u>	<u>687750100002</u>	<u>687712100002</u>	<u>687740100002</u>	<u>687745100002</u>	<u>687718152002</u>	<u>687706152002</u>
<u>687734100002</u>	<u>687725152002</u>	<u>687716100002</u>	<u>687718100002</u>	<u>687733100002</u>	<u>687728100002</u>	<u>687717152002</u>
<u>687710100002</u>	<u>687730100002</u>	<u>687725100002</u>	<u>687734152002</u>	<u>687720100002</u>	<u>687708100002</u>	<u>687732100002</u>