


**Part Number: 87433-1120**

1.00mm Pitch ZYTON™ Stacking System, Board-to-Board Receptacle, Surface Mount, Dual Row, Vertical Stacking, 21 Circuits



Series image - Reference only

Status: **OBSOLETE**
Replacement: NONE
Series: [87433](#)
Category: PCB Receptacles

Product Environmental Compliance

[EU RoHS:](#) Compliance Status Not Reviewed
[China RoHS:](#)
[REACH SVHC:](#) Not Reviewed
[Low-Halogen Status:](#) Not Reviewed

Part Detail**General**

Status	Obsolete
Category	PCB Receptacles
Series	87433
Application	Board-to-Board, Signal
Obsolete Date	2002/06/01
Product Name	Zyton™

Physical

Circuits (Loaded)	21
Circuits (maximum)	21
Flammability	94V-0
Glow-Wire Compliant	No
Material - Plating Mating	Gold
Number of Rows	2
Orientation	Vertical
PCB Retention	Yes
Packaging Type	Tube
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.762µm
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-30°C to +85°C
Termination Interface: Style	Surface Mount

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	1A
Voltage - Maximum	125V

Agency Certification

CSA	LR19980
UL	E29179

Material Info

UPC	800753542372
-----	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**

[Check our list of old tooling that used to be available for this part](#)