






SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	NO MISSING SYMBOL NUMBER	
	LAST NO. USED		
	38		
	20		

DWS STATUS		ZONE		REVISION HISTORY		AUTH		DR		APVD	
DATE	STG	REV	M/P	CHG							
29JUL02	R	04	-	-	REDRAWN TO PD & MAT'L SPEC WAS R0064366	228504	RH	RCH	RC		
10SEP02	R	04	AA	-	4.75 +0.15/-0.35 WAS 4.75 +/-0.15	230162	RH	RCH	RC		
12NOV02	R	04	AB	-	REVISED LOCK GRAPHICS	233537	RH	RH	ET		




THIS DIMENSION MAY "REDUCE" TO 20.6 DUE TO BOW ON OPEN END OF PART



OPTIONAL CONSTRUCTION

NOTES


- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE >PA66< PER SAE J1344. (1)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- MATING COMPONENTS OR EQUIVALENT: CONN & SEAL ASM 12052813
- (1)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.
- MAX CABLE DIAMETER THAT WILL FIT PART IS 3.13.



DWS TYPE		PART DRAWING	
STYLE		VOLUME (C/P)	DISTR CODE
		2,743	D
ROUTING		6900	

UNLESS OTHERWISE SPECIFIED
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994
AS AMENDED BY THE 2003 DIMENSIONING AND TOLERANCING ADDENDUM 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS ARE TO BE LOCATED ON ANY EXTERIOR SURFACE. SEPARATE POSITION ALLOWANCES MAY BE BASED SEPARATELY, REGARDLESS OF DATUM REFERENCE.
ALL DIMENSIONS ARE IN MILLIMETERS

PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	



DIMENSIONAL RANGE (MM)		CHART	
FROM	TO	1	2
0	20	1	2
20	30	1	2
30	70	1	2
70	100	1	2
100	150	1	2
150	200	1	2
200	250	1	2
250	300	1	2
300	400	1	2
TOLERANCE UNLESS OTHERWISE SPECIFIED		ANGULAR TOLERANCE 12°	
1±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2			

THIRD ANGLE PROJECTION		DO NOT SCALE	
USE MATH DATA		USE MATH DATA	

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	DATE
APVD1 R. HERMOSILLO	10SEP02
APVD2 R. CHACON	10SEP02
APVD3 R. CORZAS	12SEP02
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL: W3592025 PA66 HS 1M GRA MD	
DRAWING NAME: TPA M/P 280	
DRAWING NUMBER: 12052816	
SIZE: A0	SCALE: 5:1
FRAME NO: 1	SHEET NO: 1 OF 1
STG: R	REV: 04
M/P: AB	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[12052816-B](#)