

SIGN	DATE	DESCRIPTION	APPROVER
△	2008.12.10	Change to Operating temperature	Shi Jun

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Terminal body
- (metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating "-" slot type
- Contacts: Brass
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 30A
- Wire range:
 - Solid wire(AWG): 10-24
 - Stranded wire(AWG): 10-24
- Torque(Lb-In): 8.9
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 

RoHS Compliant

PART NUMBER:



OSTT7XX2150

No. of Poles	COLOR
02 2 Poles	0: Black
03 3 Poles	5: Green (Standard)
...	6: Blue
24 24 Poles	8: Grey

OST ON-SHORE TECHNOLOGY, INC.

TITLE		OSTT7 9.52mm Series 180D						
PART NO.		OSTT7XX2150			DWG NO.	OSTT7XX2150.DWG		
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
Shi Jun 2006.10.21		Shi Jun 2006.10.21	xionghaitao 2006.10.21	xionghaitao 2006.10.21			UNIT: mm	X. ±0.50
							SCALE: NONE	X.X ±0.30
					SHEET: 01/01		REV: F	X.XX ±0.10
								X° ±1°

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.



N=Number of poles

P.C.B LAYOUT

