


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


REVISIONS				DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
	B	REVISED & REDRAWN							
95	C	REDRAWN	HYO	2/14/00	JC	2/29/00	JC	2/29/00	



### Specifications:

1. Design Volts: 6.5
2. Design Amps: 2.75
3. Filament Shape: C-6
4. Avg. Life: 100 hours
5. Base : Two contacts bayonet
6. M.S.C.P. : 23.00
7. Watts: 17.875

SPC-F004.DWG

<b>DISCLAIMER:</b> ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.			 <b>SPC TECHNOLOGY</b>						
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:						
	J.C.	12/18/92	S-8 BAYONET BASE LAMP						
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE		REV		
	J.P.	2/2/93	A	1493	50N8130.DWG		C		
	APPROVED BY:	DATE:	SCALE: NTS		U.O.M.: INCHES [mm]		SHEET: 1 OF 1		
	J.L.	2/8/93							