



LOC		DIST		REV		REVISIONS		DATE		APP	
G	14	P	P	ZONE	LTR	DESCRIPTION					
						D	REVISED PER 0720-0230-93		2/28/94		W.D.M.



AMP WIRE RANGE		UL E13288 Listed	
16-14 AWG STRANDED		16-14 AWG STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS	
NOT CERTIFIED		NOT APPLICABLE	

△ STAMP AMP 16-14* APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		VOLTAGE RATING: NOT APPLICABLE	
FOR APPLICATION TOOLING INFORMATION		WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180] CIR MILS STRANDED	
FOR ORDER ENTRY		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE LATEST REVISION SHALL BE CONSULTED FOR THE LATEST REVISION.	

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN MILLIMETERS TOLERANCES ON: 2 PLC DEC ± .1 3 PLC DEC ± .05	
MATERIAL COPPER PER ASTM B-152 ANNEALED	
FINISH TIN PLATE 0.00254 [1.000100] MIN THK PER MIL-T-10727	

DR 1-28-93 TA BRINKMAN	
CHK 1-28-93 DA PATTERSON	
APPD 1-28-93 DE MILLER	
APPD 1-28-93 JL HECKLEY	
PRODUCT SPEC	
APPLICATION SPEC	
WEIGHT -	

AMP		AMP Incorporated Horsham, PA 17105-3608	
TERMINAL, RECTANGULAR TONGUE, BUDGET		NAME	
SIZE		CAGE CODE	
C		00779	
SCALE 10:1		DRAWING NO	
		C-35278	
		SHEET	
		1 OF 1	