



|                     |   |                            |
|---------------------|---|----------------------------|
| <b>CUSTOMER</b>     | : |                            |
| <b>DESCRIPTION</b>  | : | <b>DC BRUSHLESS BLOWER</b> |
| <b>DIMENSIONS</b>   | : | <b>35X35X7 mm</b>          |
| <b>M O D E L</b>    | : | <b>GB0535ADB2-8</b>        |
| <b>P/N</b>          | : | <b>M</b>                   |
| <b>APPROVED NO</b>  | : |                            |
| <b>APPROVED BY</b>  | : |                            |
| <b>(AUTHORIZED)</b> |   |                            |




|      |             |      |             |     |       |             |            |
|------|-------------|------|-------------|-----|-------|-------------|------------|
| DAWN | Fanny 12/15 | CHKD | Viddy 12/15 | 發行章 | APPD. | SPEC. NO.   | B350067    |
|      |             |      |             |     |       | ISSUE DATE  | 03.03.1999 |
|      |             |      |             |     |       | EDITION     | 1          |
|      |             |      |             |     |       | REVISE DATE | 12.15.2000 |
|      |             |      |             |     |       | E.SPEC      | EB10084    |

**FAX:886-7-7163086~89**


**DC BRUSHLESS BLOWER****MODEL : GB0535ADB2-8****P/N : M****CHARACTERISTICS**

1. Motor Design : Patented single-coil DC brushless 8 poles motor design.
2. Insulation Resistance : More than 500M ohm between internal stator and lead wire(+) measured by DC 500V.
3. Dielectric Strength : Applied AC 500V for one minute or AC 600V for 2 seconds between housing and lead wire(+)
4. Noise Level : Measured in an semi-an echoic chamber with background noise level below 15 dB(A). The fan is running in free air with microphone at a distance of one meter from the fan intake.
5. Input power, Current & Speed : Measured after continuous 30 minutes operation at rated voltage in clean air at ambient temperature of 25 degrees C.
6. Tolerances :  $\pm 15\%$  on rated power and current.
7. Motor Protection : Locked rotor protected.
8. Air Performance : Measured by a double chamber. The value are recorded when the fan speed is stabilized at rated voltage.



建準電機工業股份有限公司  
SUNONWEALTH ELECTRIC  
MACHINE INDUSTRY CO., LTD

|            |              |             |            |
|------------|--------------|-------------|------------|
| SPEC. NO.  | B350067      | REVISE DATE | 89. 12. 15 |
| ISSUE DATE | 03. 03. 1999 | EDITION     | 2. 27      |
| PAGE       | 2 OF 8       |             |            |



## SPECIFICATIONS

MODEL : GB0535ADB2-8

P/N : M

- 1-1. Rated Voltage : 5 VDC
- 1-2. Operating Voltage Range : 3-6 VDC
- 1-3. Starting Voltage : 3 VDC
- 1-4. Speed (Reference Value) : 6500 RPM
- 1-5. Air Delivery : 1.0 CFM
- 1-6. Static Pressure : 0.22 Inch-H<sub>2</sub>O
- 1-7. Rated Current : 0.08 AMP
- 1-8. Rated Power : 0.4 WATTS
- 1-9. Noise Level : 25 dB(A)
- 1-10. Direction of Rotation : Counter-clockwise viewed front fan blade
- 1-11. Operating Temperature : -10 to +90 Deg.C
- 1-12. Storage Temperature : -40 to +90 Deg.C
- 1-13. Bearing System : Precise ball bearing system
- 1-14. Weight : 12g
- 1-15. Safety : UL/CUR/TUV/CE Approvals
- 1-16. Vibration : Vibration of acceleration 1.5G and Frequency 5~50~5Hz is applied in the 3 directions(X,Y,Z) for 30 minutes, each Direction at the cycle of 1 minute.




建準電機工業股份有限公司  
SUNONWEALTH ELECTRIC  
MACHINE INDUSTRY CO., LTD

|            |              |
|------------|--------------|
| SPEC. NO.  | B350067      |
| ISSUE DATE | 03. 03. 1999 |
| PAGE       | 3 OF 8       |

REVISE DATE 12.15.1999

E D I T I O N 1




MODEL : GB0535ADB2-8

P/N : M

# PERFORMANCE CURVES


STATIC  
PRESSURE



建準電機工業股份有限公司  
SUNONWEALTH ELECTRIC  
MACHINE INDUSTRY CO., LTD


|            |              |
|------------|--------------|
| SPEC. NO.  | B350067      |
| ISSUE DATE | 03. 03. 1999 |
| PAGE       | 4 OF 8       |

|             |            |
|-------------|------------|
| REVISE DATE | 12.15.2000 |
| EDITION     | 1.0        |



**MATERIAL**

|                |   |                                             |
|----------------|---|---------------------------------------------|
| 2-1. Frame     | : | DIE-CAST ALUMINUM                           |
| 2-2. Impeller  | : | Thermoplastic PBT of UL 94V-0               |
| 2-3. Bobbin    | : | Thermoplastic PBT of UL 94V-0               |
| 2-4. Lead Wire | : | UL3265,28AWG,+RED;-BLACK<br>YELLOW:3rd wire |

**DIMENSIONS**

1.One directional exhaust


2.The Best Mounting Direction: Fan blade face up or shaft horizontal direction.

UNITS : mm


建準電機工業股份有限公司  
SUNONWEALTH ELECTRIC  
MACHINE INDUSTRY CO., LTD

|            |              |
|------------|--------------|
| SPEC. NO.  | B350067      |
| ISSUE DATE | 03. 03. 1999 |
| PAGE       | 5 OF 8       |

|             |            |
|-------------|------------|
| REVISE DATE | 12.15.2000 |
| EDITION     | 1          |
|             | 89.12.21   |



發行章



T=1 Rotation

$$T=T_1+T_2+T_3+T_4+T_5+T_6+T_7+T_8=(1 \text{ Rotation})$$


$$T_1=T_2=T_3=T_4=T_5=T_6=T_7=T_8=\frac{60}{8(\text{rpm})}$$



建準電機工業股份有限公司  
SUNONWEALTH ELECTRIC  
MACHINE INDUSTRY CO., LTD

|            |              |
|------------|--------------|
| SPEC. NO.  | B350067      |
| ISSUE DATE | 03. 03. 1999 |
| PAGE       | 6 OF 8       |

|             |            |
|-------------|------------|
| REVISE DATE | 12.15.2000 |
| EDITION     | 89.12.21   |





## FAN 3rd WIRE SIGNAL

Fan with switching driving circuit designed for rpm measurement:

These fan motors have three lead wires:(+:Red,-:Black,output signal for 3rd wire:Yellow)

- ◆ M Type
- ◆ Low voltage start-up
- ◆ 3rd wire square wave signal was amplified by a transistor (open collector type)



$V_{cc}=+ 7.5 \text{ V max}$

$I_c = 10\text{mA max}$

$V_{ce(sat)}=0.5\text{V max}$

$$I_c = \frac{V_{cc} - V_{ce(sat)}}{R_L} \leq 10\text{mA}$$



建準電機工業股份有限公司  
SUNONWEALTH ELECTRIC  
MACHINE INDUSTRY CO., LTD.

|            |              |
|------------|--------------|
| SPEC. NO.  | B350067      |
| ISSUE DATE | 03. 03. 1999 |
| PAGE       | 7 OF 8       |

|             |            |
|-------------|------------|
| REVISE DATE | 89. 12. 21 |
| EDITION     | 89. 12. 21 |

發行章

## Notes

1. SUNON will not guarantee the products if the application of our products is exceeded the limitation which is specified on this specification.
2. In case of change of the specification specified on this document, a written notice is requested in advance.
3. Please do not touch the impeller with pressure and never bring the fan with lead wire. The bearings and lead wire may be damaged.
4. No guarantee on the products against the safety problem or failure caused by powder dust, drop of water or insect.
5. If there is any data or related documentation different from this data sheet, this data sheet is the principal reference.
6. For the purpose of MIS, please indicate SPEC No. on every order.
7. In case of the fan has no polarity protection function, wires with same color (electrode) must be connected together during the assembly. (i.e. red + red, black + black) or the fan will be damaged immediately.
8. Please do not use the fan in the environment of corrosive gas or liquid or any detrimental gas.
9. Please do not store the fan in the environment of high / low temperature, high humidity or any detrimental gas. Please store the fan within 6 months, every 6 months, there shall be a linkage of electric current to the fan, even though the fan is stored in room temperature.
10. While the fan is in operation, please do not lock the fan intentionally for a long period of time, since the continuous stoppage will result in over-heat and damage of the fan.
11. During the installation of the fan, please pay substantial attention to possible noise cause by resonance vibration and vibration.
12. During the testing of the fan, please be sure to use finger guard to insure safety.
13. Unless otherwise specified, if there is any doubt in the judgement, the temperature and relative humidity range of environment will be take in according to the standard test condition as 25°C and 65%.

建準電機工業股份有限公司  
SUNONWEALTH ELECTRIC  
MACHINE INDUSTRY CO., LTD.

|            |              |             |            |
|------------|--------------|-------------|------------|
| SPEC. NO.  | B350067      | REVISE DATE | 12.15.2000 |
| ISSUE DATE | 03. 03. 1999 | EDITION     | 1          |
| PAGE       | 8 OF 8       |             |            |



發行章