




A circuit variation of Normal Open and Normal Close.



■ Typical Specifications

Items		Specifications
Rating (max.) / (min.) (Resistive load)		1mA 5V DC / 50 μ A 3V DC
Contact resistance (Initial / After operating life)		2 Ω max. / 5 Ω max.
Operating force		0.35N max.
Operating life	Without load	50,000cycles
	With load	50,000cycles (1mA 5V DC)


■ Product Line

Poles	Positions	Terminal type	Lever length	Operating direction	Circuit	Location lug	Flame leg	Minimum order unit (pcs.)		Product No.	Drawing No.
								Japan	Export		
1	1	For PC board (Reflow)	Standard	Right	N / O	With	With	5,000	20,000	SPVS310100	1
						Without				SPVS310200	
					N / C	With				SPVS320100	2
						Without				SPVS320200	
				Left	N / O	With				SPVS410100	3
						Without				SPVS410200	
					N / C	With				SPVS420100	4
						Without				SPVS420200	
			Long	Right		With				SPVS360100	5
						Without				SPVS360200	

■ Packing Specifications

Taping

Unit:mm



Number of packages (pcs.)			Tape width (mm)	Export package measurements (mm)
1 reel	1 case / Japan	1 case / export packing		
5,000	10,000	20,000	16	417 × 409 × 139

■ Dimensions

Unit:mm

No.	Style	PC board mounting hole and land dimensions (Viewed from direction A)
1	Right operation type With boss	

Detector
Slide
Push
Rotary
Encoders
Power
Dual-in-line Package Type
TACT Switch™

No.	Style	PC board mounting hole and land dimensions (Viewed from direction A)
2	Right operation type With boss	
3	Left operation type With boss	
4	Left operation type With boss	
5	Right operation type With boss	

Note

Dimensions drawing is for type with location lugs.

■ Circuit Diagram






Circuit Diagram		
Control direction	Push ON (N/O)	Push OFF (N/C)
Right	Drawing No.1 	Drawing No.2,5
Left	Drawing No.3 	Drawing No.4

Terminal Layout (Viewed from Direction A)

Control direction		Push ON (N/O) Push OFF (N/C)
Right	Drawing No.1,2,5  (COMMON)	
Left	Drawing No.3,4  (COMMON)	

Detector Switches

■ List of Varieties (General-purpose Type)

Series		General-purpose Type					
		SPVS	SPVN	SPVP	SPVT	SPVM	SPVR
Photo							
Operation type		Two-way		One-way	Two-way		
Dimensions (mm)	W	3.5	3.8	3.5	5.6	2.8	3.6
	D	3.3	3.6	5.65	4.7	3.5	4.2
	H	1		1.2	1.9	1.5	1.2
Operating temperature range		-40°C to +85°C					
Automotive use		●	●	●	●	●	●
Life cycle (availability)							
Poles / Positions		1 / 1					
Rating (max.) (Resistive load)		1mA 5V DC			50mA 20V DC	1mA 5V DC	
Rating (min.) (Resistive load)		50μA 3V DC		100μA 3V DC		50μA 3V DC	100μA 3V DC
Durability	Operating life without Load	50,000cycles 5 Ω max.		50,000cycles 10 Ω max.	100,000cycles 1 Ω max.	50,000cycles 5 Ω max.	
	Operating life with Load Rating (max.) (Resistive load)	50,000cycles 5 Ω max.		50,000cycles 10 Ω max.	100,000cycles 1 Ω max.	50,000cycles 5 Ω max.	
Electrical performance	Initial contact resistance	2 Ω max.		5 Ω max.	500mΩ max.	2 Ω max.	3 Ω max.
	Insulation resistance	100MΩ min. 100V DC					
	Voltage proof	100V AC for 1 minute					
Mechanical performance	Terminal strength	0.5N for 1minute				1N for 1minute	0.5N for 1minute
	Actuator strength	5N			10N	5N	2N
Environmental performance	Cold	-40±2°C for 96h					
	Dry heat	85±2°C for 96h					
	Damp heat	40 ± 2°C, 90 to 95% RH for 96h					
Operation force		0.35N max.		0.55N max.	0.4N max.		0.35N max.
Page		13	15	17	18	21	23

- Detector Switches Soldering Conditions 66
- Detector Switches Cautions 67

Note

- indicates applicability to all products in the series.

Detector

Slide

Push

Rotary

Encoders


Power

Dual-in-line
Package Type

TACT Switch™

Example of Reflow Soldering Condition

1. Heating method: Double heating method with infrared heater.
2. Temperature measurement: Thermocouple 0.1 to 0.2 φ CA (K) or CC (T) at soldering portion (copper foil surface).
A heat resisting tape should be used for fixed measurement.
3. Temperature profile



Series (Reflow type)	A (°C) 3s max.	B (°C)	C (s)	D (°C)	E (°C)	F (s)
SPPB	250	230	40	180	150	120
SPPW8			35			
SPVE	260		40			
SPVL						
SPVM						
SPVN						
SPVP						
SPVR						
SPVS						
SPVT						
SSCM						
SSCQ						
SPVQC	250					

Notes

1. The condition mentioned above is the temperature on the mounting surface of a PC board. There are cases where the PC board's temperature greatly differs from that of the switch, surface depending on the PC board's material, size, thickness, etc. The above-stated conditions shall also apply to switch surface temperatures.
2. Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

Reference for Hand Soldering

Series	Soldering temperature	Soldering time
SPVS, SPVN, SPVP, SPVT, SPVM, SPVR, SPVE, SPPW8, SSCQ, SSCM, SPVL, SSCT, SPVQC	350 ± 5°C	3s max.
SPVQ1, SPVQ3, SPVQ6, SPVQ7, SPVQ8, SPVQ9, SSCN, SPVQA	300 ± 10°C	3 + 1 / 0s
SPPB	350 ± 5°C	5s max.
SSCF	350 ± 10°C	3 + 1 / 0s

Reference for Dip Soldering (For PC board terminal types)

Series	Items		Dip soldering	
	Preheating temperature	Preheating time	Soldering temperature	Duration of immersion
SSCT, SPVQ1, SPVQ3, SPVQ6, SPVQ7, SPVQ8, SPVQ9, SPVQA	100 ± 10°C	60s max.	260 ± 5°C	5 ± 1s
SPPW8, SPPB	100°C max.	60s max.	255 ± 5°C	5 ± 1s
SSCF	—	—	260 ± 5°C	5 ± 1s