

TG/LTG-Series



The TG-Series Mini Tippette rocker switches are single or double pole and feature an all nylon double-insulated construction. These switches are designed with snap-in mounting for fast, low cost assembly. The illuminated version (LTG) is available with either a paddle or rocker actuator. These AC rated switches are also suitable for low-voltage DC applications.

- Specifications
- Certifications*: UL, CSA, VDE
 - Dielectric Strength: 1,000 V (minimum)
 - Insulation Resistance: 100 Megohms (minimum)
 - Base Material: Nylon
 - Actuator Material: Nylon or Polycarbonate
 - Bezel Material: Nylon

* Due to ongoing technological advances, consult factory for certification specifics.


Dimensional Specifications: in. [mm]



LTG		G	O	50	1	-	T	B	-	B	-	R	/	125N
SERIES		RATING			ACTUATOR STYLE		ACTUATOR COLOR ²			BASE COLOR ²				
TG	DOUBLE POLE	40	5A 250VAC	10A 125VAC	P	PADDLE	B	BLACK	B	BLACK	W	WHITE		
	NON-LIGHTED		W					WHITE						
LTG	DOUBLE POLE	41	1/2HP 125-250VAC	10(4)A 250VAC μ	T	ROCKER								
	W/INDICATOR LIGHTS													
CIRCUIT ¹		50			TERMINATION/FUNCTION					LENS COLOR ³				
See Circuit Designation Chart Page 39		50	10A 250VAC	15A 125VAC	3/4HP 125-250VAC	FUNCTION	SOLDER LUG	.250	.187	WIRE				
			TAB (QC)					TAB (QC)	LEAD					
CENTER POSITION		51	10A 250VAC	15A 125VAC		ON-NONE-OFF	0	1	3	5				
			(ON)-NONE-OFF				A	B	D	F				
						ON-NONE-(OFF)	L	M	R	T				
							ON-NONE-ON	0	1	3				
						ON-NONE-(ON)	A	B	D	F				
							ON-OFF-ON	0	1	3				
C	CENTER OFF													
	THREE POSITION													
O	NO CENTER OFF													
	TWO POSITION													
NOTES:														
Shading indicates standard configurations.														
Imprinting is available. Please specify when ordering.														
Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in														

NOTES:
Shading indicates standard configurations.
Imprinting is available. Please specify when ordering.
Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.
1 TG available with circuits A, B, C, D, E, F.
LTG available with circuits G, H, I, J, M, N, P, Q, R, T, U, V, Y, Z.
3 Custom colors are available. Consult factory.
4 Specify lens color for LTG-Series only.

Circuit Designation Chart - refers to TG/LTG, TTG and TLG-Series Switches pages 36-38



● CONTACT TERMINAL
Will make contact with switching lever

● CONTACT TERMINAL AND SWITCH LEVER

○ ISOLATED TERMINAL
Does not make contact with switching lever

○ BULB

NOTES:
For variations to above circuits, consult factory.