


DO NOT SCALE

DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION



REV

REVISION RECORD

DATE

DW

APD

01

REVISED PER ECO-09-020935

04SEP09

KK


AEG

NOTES





1 FOR USE ON MINIATURE APPLICATORS (LEFT-RIGHT FEED)
AND STANDARD APPLICATORS (RIGHT-LEFT FEED).

2 REELED WITH PAPER COVER.

3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



for 0,8 mm tab
thickness. -



3 OBSOLETE

1

TINPLATED

PH.BRONZE

160918-4

1

UNPLATED

PH.BRONZE

160918-3

1

TINPLATED

BRASS

160918-2

1

UNPLATED

BRASS

160918-1

NOTES

FINISH

MATERIAL

PARTNUMBER

CUSTOMER
DRAWING

AMP

AMP-HOLLAND B.V.
's-Hertogenbosch, The Netherlands.

FOR REFERENCE ONLY
WILL NOT BE UPDATED

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION sept, 1987

© COPYRIGHT 1987 BY AMP-HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED.
AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR
PATENTS PENDING.

DR.

DATE

R.v.Lokven

17.09.87

WIRE RANGE

0,5-1,0 mm²

NAME

.110 SRS FASTON RECEPTACLE.

REV.DATE

D M Y

CHK.

DATE

A.B.

18.09.87

INSUL.RANGE

1,4-2,3mmDIA

17

09

87

APP.

DATE

L.v.Soest

22.09.87

SIZE

A3

SHEET

1 OF 1

DWG. No.

160918

REV.LTR.

01

8

7

6

5

4

3

2

1