

NOTES:

1.0 ELECTRICAL SPECIFICATIONS:

1.1 FREQUENCY RANGE: DC to 4.0 GHz

1.2 VSWR: 1.25:1 MAX.

1.3 IMPEDANCE: 50 OHMS

1.4 POWER: 2 WATTS AVG. AT +25°C


DERATED LINEARLY TO 0.5 WATTS AT +125°C

1.5 OPERATING TEMP. RANGE: -54°C to +125°C

2.0 MARKING

2.1 MARK UNIT AS SHOWN:

3.0 DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.



REV.	DESCRIPTION	DATE
	RELEASED	8/12/93
-1	ADDED TITLEBLOCK	10/28/05
C	ECO 23006	12/10/10

NOTICE: The information contained in this drawing is proprietary and must not be used without the permission of Emerson Network Power.

UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:
 3 PLACE DECIMALS $\pm .005$
 2 PLACE DECIMALS $\pm .02$
 FRACTIONS $\pm 1/64$
 PARALLELITY: T.I.R. _____
 FLATNESS: T.I.R. _____
 CONCENTRICITY: T.I.R. _____
 ANGLES AND PERPENDICULARITY: $\pm 1^\circ$

CAGE CODE **34078** *MIDWEST MICROWAVE*

EMERSON
Network Power
Connectivity Solutions

DRAWN/DATE
A.BEATTY
8/4/93

ENG./DATE
G.KOZAK
8/10/93

CHECKED/DATE
M.HOLLMAN
8/6/93

APPROVED/DATE
REV.
TRM-2071-M0-NNN-07-01 C

SCALE: 5=1 SHEET 1 of 1

TERMINATION
OUTLINE DRAWING