

IL series

Sealed pushbutton switches for thick panels - long bushing Ø 12 mm - momentary

Distinctive features and specifications



- ☐ Momentary pushbuttons for thick panels
- ☐ Illuminated or non-illuminated
- ☐ Tactile feedback
- ☐ Flat round actuator for optional marking
- ☐ Sealed to IP67

ENVIRONMENTAL SPECIFICATIONS

- Front panel sealing : IP67 according to IEC 60529
- Shock resistance : 100 g according to IEC 512-4, test 6c
- Vibration resistance : 10-500 Hz - 10 g according to IEC 512-4, test 6d
- Salt spray : IEC 512-6, test 11f
- Operating temperature : -40°C to +85°C

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
2A 24VDC, 200.000 cycles
- Initial contact resistance : 50 mΩ max.
- Insulation resistance : 1 GΩ min. at 500VDC
- Dielectric strength : 1.000 Vrms

LED COMPONENT SPECIFICATIONS

LED colour	Forward current	Typ. forward voltage	Max. forward voltage
Super red (LOS)	20mA	2,1V	2,3V
Yellow (LOY)	20mA	2,1V	2,3V
Green (LOG)	20mA	2,1V	2,3V
Blue (LOB)	20mA	3,2V	3,8V
White (LOW)	20mA	3,35V	4,25V

A resistor must be series-connected by the user.

Resistor value = $\frac{\text{supply voltage} - \text{LED forward voltage}}{\text{LED forward current}}$

GENERAL SPECIFICATIONS


- Panel thickness : 1,50 mm (.059) min.
10 mm (.393) max.
- Total travel :
1,7 mm (.067) +/- 0,3 mm
- Typical operating force :
4N +/- 2N
- Low level or mechanical life :
1.000.000 cycles
- Torque : 1 Nm max. applied to nut
- Soldering : 300°C max. for
3 seconds

MATERIALS

- Case : thermoplastic UL94-V0
- Actuator : polyamide 6/6
- Bushing/bezel : polyamide 6/6
- Contacts : silver, gold plated
- Terminal seal : epoxy


MOUNTING

Panel cut-out




① Flat seal

Matrix mounting



Back of panel space requirement




Tolerance : The general tolerance for dimensions in this brochure is $\pm 0,3$ (.012).

Dimensions, specifications and data shown in this brochure are subject to change without notice.

IL series

Sealed pushbutton switches for thick panels - long bushing Ø 12 mm - momentary

Overview



ABOUT THIS SERIES

On the following pages, you will find successively :
 - model structure of switches and options in the same order as in above chart

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



NOTICE : please note that not all combinations of above numbers are available.
 Refer to the following pages for further information.



Mounting accessories : Standard hardware supplied : 1 flat seal and 1 hex nut 14 mm (.551) across flats.
 Hex nut part number U166.




Packaging unit : 25 pieces

IL series

Sealed pushbutton switches for thick panels - long bushing Ø 12 mm - momentary


Illuminated




CILLFCT

- Curved or flat actuator
- Antirotation bushing

Straight P



MODEL
STRUCTURE



Actuator marking available on ILP models (symbol 10 mm max.). On request.

Solder lug terminals



Curved actuator
ILR3SAD




Normally open

Flat actuator
ILP3SAD



Normally open

→ Flat



Also available with straight PC terminals : **IL•3PAD**

Flying lead terminals



Curved actuator
ILR3FAD




Normally open

Flat actuator
ILP3FAD




Normally open

→ Flat




ACTUATOR COLOUR



1 : blue - 2 : black - 3 : green - 4 : grey - 5 : yellow - 6 : red - 7/1 : white - 8 : bright chrome
9 : orange - B : dark blue - M : brown

LED COLOUR




LOS : red - LOY : yellow - LOG : green - LOB : blue - LOW : white

IL series

Sealed pushbutton switches for thick panels - long bushing Ø 12 mm - momentary


Non-illuminated




CILFCT

- Curved or flat actuator
- Antirotation bushing

Straight P



MODEL
STRUCTURE



Actuator marking available on ILP models (symbol 10 mm max.). On request.

Solder lug terminals



Curved actuator
ILR3SAD




Normally open

Flat actuator
ILP3SAD



Normally open

→ Flat



Also available with straight PC terminals : **IL•3PAD**

Flying lead terminals



Curved actuator
ILR3FAD




Normally open

Flat actuator
ILP3FAD




Normally open

→ Flat



ACTUATOR COLOUR



1 : blue - 2 : black - 3 : green - 4 : grey - 5 : yellow - 6 : red - 7/1 : white - 8 : bright chrome
9 : orange - B : dark blue - M : brown

Reduced bezel for compact matrix mounting - option X1242



ILP3FAD...X1242

- Dia. 15 (.590) reduced bezel
- **Mounting from the front into a threaded panel cut-out**
- Matrix mounting : 16 x 16 mm (.630x.630)
- Illuminated or non-illuminated
- Same terminal options and colours as standard models
- Part numbers on request.

Reduced bezel for compact matrix mounting - option 234



ILP3SAD...234

- Dia. 15 (.590) reduced bezel
- **Standard panel mounting**
- Matrix mounting : 18 x 18 mm (.708x.708)
- Illuminated or non-illuminated
- Same terminal options and colours as standard models
- Part numbers on request.