

Surface Mount Glass Passivated Rectifier

Major Ratings and Characteristics

$I_{F(AV)}$	1.0 A
V_{RRM}	50 V to 1000 V
I_{FSM}	40 A, 30 A
I_R	1.0 μ A, 5.0 μ A
V_F	1.1 V
T_j max.	150 °C



DO-214AC (SMA)

Features

- Low profile package
- Ideal for automated placement
- Glass passivated chip junction
- Low forward voltage drop
- Low leakage current
- High forward surge capability
- Meets MSL level 1, per J-STD-020C
- Solder Dip 260 °C, 40 seconds



Mechanical Data

Case: DO-214AC (SMA)

Epoxy meets UL-94V-0 Flammability rating

Terminals: Matte tin plated leads, solderable per J-STD-002B and JESD22-B102D

E3 suffix for commercial grade, HE3 suffix for high reliability grade (AEC Q101 qualified)

Polarity: Color band denotes cathode end

Typical Applications

For use in general purpose rectification of power supplies, inverters, converters and freewheeling diodes for consumer, automotive and Telecommunication

Maximum Ratings

($T_A = 25$ °C unless otherwise noted)

Parameter	Symbol	S1A	S1B	S1D	S1G	S1J	S1K	S1M	Unit
Device marking code		SA	SB	SD	SG	SJ	SK	SM	
Maximum recurrent peak reverse voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current (see fig.1)	I _{F(AV)}	1.0							A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	40					30		A
Operating junction and storage temperature range	T _J , T _{STG}	- 55 to + 150							°C

Electrical Characteristics

($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

Parameter	Test condition	Symbol	S1A	S1B	S1D	S1G	S1J	S1K	S1M	Unit
Maximum instantaneous forward voltage	at 1.0 A	V _F	1.1							V
Maximum DC reverse current at Rated DC blocking voltage	T _A = 25 °C	I _R	1.0					5.0		μA
	T _A = 125 °C		50							
Typical reverse recovery time	at I _F = 0.5 A, I _R = 1.0 A, I _{rr} = 0.25 A	t _{rr}	1.8							μs
Typical junction capacitance	at 4.0 V, 1 MHz	C _J	12							pF

Thermal Characteristics

($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	S1A	S1B	S1D	S1G	S1J	S1K	S1M	Unit
Typical thermal resistance ⁽¹⁾	R _{θJA}	75					85		°C/W
	R _{θJL}	27					30		

Notes:

(1) Thermal resistance from junction to ambient and from junction to lead mounted on P.C.B. with 0.2 x 0.2" (5.0 x 5.0 mm) copper pad areas

Ratings and Characteristics Curves

($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)




Figure 1. Forward Current Derating Curve




Figure 2. Maximum Non-Repetitive Peak Forward Surge Current




Figure 3. Typical Instantaneous Forward Characteristics




Figure 5. Typical Junction Capacitance




Figure 4. Typical Reverse Leakage Characteristics






Figure 6. Typical Transient Thermal Impedance

Package outline dimensions in inches (millimeters)





Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.