



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		G	ECO-07-000840	17JAN2007	LAM	AWF

D


C

B


A



1. WIRE RANGE 22-26 AWG.
 2. INSULATION RANGE 0.91-1.37 [.036-.054] DIA.
- 3 PREPLATED 0.00127 [.000050] MIN TIN-LEAD IN ZONES I & II, 0.000762 [.000030] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
 - 4 PREPLATED 0.00127 [.000050] MIN TIN-LEAD IN ZONES I & II, 0.00127 [.000050] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
 - 5 PHOSPHOR BRONZE.
 - 6 ZONE I (OUTSIDE SURFACES).
 - 7 ZONE II (INSIDE SURFACES).
 - 8 ZONE III (INSIDE SURFACES).
 - 9 MAXIMUM CUTOFF.



SECTION A-A



SECTION B-B

OBSOLETE	4	-	531216-5
	4	531216-4	531216-3
	3	531216-2	531216-1
	FINISH	LOOSE PIECE PART NO	STRIP PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER 08JAN99	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
		CHK S. BOLASH 08JAN99				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S. BOLASH 08JAN99	NAME CONTACT, RECEPTACLE, LOW PRESSURE MINI-TANDEM SPRING			
	0 PLC ± -	PRODUCT SPEC 108-25031				
	1 PLC ± -	APPLICATION SPEC 114-25021				
	2 PLC ± -					
	3 PLC ± 0.13 [.005]		SIZE A2	CAGE CODE 00779	DRAWING NO C=531216	RESTRICTED TO -
	4 PLC ± -					
MATERIAL 531216-4	FINISH -	WEIGHT -				
		CUSTOMER DRAWING				
		SCALE 4:1	SHEET 1		OF 1	REV G

D

C

B

A

531216