




Low Power Schottky Diode



Features:

- Very low turn-on voltage and ultra-fast switching diodes, suitable for UHF detectors and other high frequency switching circuits
- Supplied on 8mm tape

SOT-23 Formed SMD Package



Pin Configuration

- 1 = Anode
- 2 = NC
- 3 = Cathode

Absolute Maximum Ratings (per Diode):

Description	Symbol		Values	Unit
Continuous reverse voltage	V_R	Max.	30	V
Forward current (DC)	I_F		200	mA
Forward voltage at $I_F = 10\text{mA}$	V_F	<	400	mV
Reverse recovery time when switched from $I_F = 10\text{mA}$ to $I_R = 10\text{mA}$; $R_L = 100\Omega$; measured at $I_R = 1\text{mA}$	t_{rr}	<	5	ns
Junction temperature	T_j	Max.	125	$^{\circ}\text{C}$

Ratings (at $T_A = +25^{\circ}\text{C}$ unless otherwise specified)

Description	Symbol		Values	Unit
Continuous reverse voltage	V_R	Max.	30	V
Forward current (DC)	I_F		200	mA
Repetitive peak forward current	I_{FRM}		300	
Non-Repetitive peak forward current $t < 1\text{s}$	I_{FSM}		600	
Storage temperature	T_{stg}	-55°C to $+150^{\circ}\text{C}$		
Junction temperature	T_j	Max.	125	$^{\circ}\text{C}$

Thermal Resistance

From junction to ambient; mounted on a ceramic substrate of $10\text{mm} \times 8\text{mm} \times 0.6\text{mm}$	$R_{th(j-a)}$	=	430	K/W
---	---------------	---	-----	-----

Low Power Schottky Diode




Characteristics $T_A = 25^\circ\text{C}$ unless otherwise specified

Description	Symbol		Values	Unit
Forward voltage $I_F = 0.1\text{mA}$ $I_F = 1\text{mA}^*$ $I_F = 10\text{mA}$ $I_F = 30\text{mA}^*$ $I_F = 100\text{mA}$	V_F	Max. Max. Max. Max. Typ. Max.	240 320 400 500 500 1,000	mV
Reverse current $V_R = 25\text{V}$	I_R	<	2	μA
Reverse breakdown voltage	$V_{(BR)R}$	>	30	V
Diode capacitance $V_R = 1\text{V}$; $f = 1\text{MHz}$	C_d	<	15	pF
Reverse recovery time when switched from $I_F = 10\text{mA}$ to $I_R = 10\text{mA}$; $R_L = 100\Omega$; measured at $I_R = 1\text{mA}$	t_{rr}	<	5	ns

* Temperature coefficient of forward voltage:

-0.6% K at $I_F = 1\text{mA}$

-0.3% K at $I_F = 30\text{mA}$



Height (mm)	Width (mm)	Depth (mm)
1.12	3.05	2.5

Dimensions : Millimetres

Part Number Table

Description	Connection	V_{RRM} Max (V)	I_F Max (mA)	V_F Max. (V) at $I_F = 10\text{mA}$	Device Marking	Package	Part Number
Diode, Schottky, Dual	Double Diode	30	200	0.4	42	SOT - 23	TBAT54A
					L43		TBAT54C

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.