







	1.484	37.69	14	4-644897-4
	1.384	35.15	13	4-644897-3
	1.284	32.61	12	4-644897-2
	1.184	30.07	11	4-644897-1
	1.084	27.53	10	4-644897-0
	.984	24.99	9	3-644897-9
	.884	22.45	8	3-644897-8
	.784	19.91	7	3-644897-7
	.684	17.37	6	3-644897-6
	.584	14.83	5	3-644897-5
	.484	12.29	4	3-644897-4
	.384	9.75	3	3-644897-3
	.284	7.21	2	3-644897-2
	1.484	37.69	14	1-644897-4
	1.384	35.15	13	1-644897-3
	1.284	32.61	12	1-644897-2
	1.184	30.07	11	1-644897-1
	1.084	27.53	10	1-644897-0
	.984	24.99	9	644897-9
	.884	22.45	8	644897-8
	.784	19.91	7	644897-7
	.684	17.37	6	644897-6
	.584	14.83	5	644897-5
	.484	12.29	4	644897-4
	.384	9.75	3	644897-3
	.284	7.21	2	644897-2
	IN	MM	NO OF POSITIONS	PART NUMBER
	L		HEADER ASSEMBLY	

RECOMMENDED MOUNTING HOLE PATTERN
FOR .063 THK PRINTED CIRCUIT BOARD

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. K. WHITAKER CHK. D. BOSSI APVD. D. BOSSI		27/JUNE/2005 27/JUNE/2005 27/JUNE/2005		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH		NAME CST-100 SHROUDED HEADER ASSEMBLY, FRICTION LOCK, STRAIGHT POST, .000030 GOLD		SIZE A1	
		PRODUCT SPEC — APPLICATION SPEC —		CAGE CODE 00779		DRAWING NO C-644897	
MATERIAL 		WEIGHT —		RESTRICTED TO —		SCALE 10:1	
  		CUSTOMER DRAWING		SHEET 1 OF 1		REV G	