



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089

NTE38 (PNP) & NTE175 (NPN) Silicon Complementary Transistors High Voltage, Medium Power Switch TO66 Type Package

Description:

The NTE38 (PNP) and NTE175 (NPN) are complementary silicon transistors in a TO66 type package designed for high-speed switching and linear amplifier applications for high-voltage operational amplifiers, switching regulators, converters, inverters, deflection stages, and high fidelity amplifiers.

Features:

- TO66 Type Package
- Collector-Emitter Sustaining Voltage:
NTE38: $V_{CEO(sus)} = 350V @ I_C = 200mA$
NTE175: $V_{CEO(sus)} = 300V @ I_C = 200mA$
- Second Breakdown Collector Current:
NTE38 $I_{S/b} = 875mA @ V_{CE} = 40V$
NTE175 $I_{S/b} = 350mA @ V_{CE} = 100V$
- Usable DC Current Gain to 2.0Adc

Absolute Maximum Ratings:

Collector-Emitter Voltage, V_{CEO}	
NTE38	350V
NTE175	300V
Collector-Base Voltage, V_{CB}	
NTE38	400V
NTE175	500V
Emitter-Base Voltage, V_{EB}	
6Vdc	
Collector Current, I_C	
Continuous	2A
Peak (Note 1)	5A
Base Current, I_B	
1A	
Total Power Dissipation ($T_C = +25^{\circ}C$), P_D	
35W	
Derate above $25^{\circ}C$	
0.2W/ $^{\circ}C$	
Operating Junction Temperature Range, T_J	
-65° to $+200^{\circ}C$	
Storage Junction Temperature Range, T_{stg}	
-65° to $+200^{\circ}C$	
Thermal Resistance, Junction to Case, $R_{\theta JC}$	
5 $^{\circ}C/W$	

Note 1. Pulse Test (NTE175 Only): Pulse Width = 5ms, Duty Cycle $\leq 10\%$.

Electrical Characteristics: ($T_C = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF Characteristics (Note 2)						
Collector–Emitter Sustaining Voltage NTE38	$V_{CEO(sus)}$	$I_C = 200\text{mA}, I_B = 0$	350	–	–	V
NTE175			300	–	–	V
Collector–Emitter Sustaining Voltage NTE38 Only	$V_{CEX(sus)}$	$I_C = 200\text{mA}, V_{BE} = -1.5\text{V}, L = 10\text{mH}$	400	–	–	V
	$V_{CER(sus)}$	$I_C = 200\text{mA}, I_B = 0, R_{BE} = 50\Omega$	375	–	–	V
Emitter–Base Breakdown Voltage NTE38 Only	V_{EBO}	$I_E = 0.5\text{mA}, I_C = 0$	6	–	–	V
Collector Cutoff Current	I_{CEO}	$V_{CE} = 150\text{V}, I_B = 0$	–	–	5	mA
Collector Cutoff Current NTE38	I_{CEV}	$V_{CE} = 250\text{V}, V_{BE(off)} = 1.5\text{V}$	–	–	0.5	mA
		$V_{CE} = 250\text{V}, V_{BE(off)} = 1.5\text{V}, T_C = +100^\circ\text{C}$	–	–	5.0	mA
		$V_{CE} = 315\text{V}, V_{BE(off)} = 1.5\text{V}$	–	–	0.5	mA
		$V_{CE} = 315\text{V}, V_{BE(off)} = 1.5\text{V}, T_C = +100^\circ\text{C}$	–	–	5.0	mA
		$V_{CE} = 360\text{V}, V_{BE(off)} = 1.5\text{V}$	–	–	0.5	mA
		$V_{CE} = 360\text{V}, V_{BE(off)} = 1.5\text{V}, T_C = +100^\circ\text{C}$	–	–	5.0	mA
NTE175	I_{CEX}	$V_{CE} = 450\text{V}, V_{BE(off)} = 1.5\text{V}$	–	–	1.0	mA
		$V_{CE} = 300\text{V}, V_{BE(off)} = 1.5\text{V}, T_C = +150^\circ\text{C}$	–	–	3.0	mA
Emitter Cutoff Current	I_{EBO}	$V_{EB} = 6\text{V}, I_C = 0$	–	–	0.5	mA
ON Characteristics (Note 2)						
DC Current Gain NTE38	h_{FE}	$I_C = 1\text{A}, V_{CE} = 4\text{V}$	10	–	100	
NTE175		$I_C = 0.1\text{A}, V_{CE} = 10\text{V}$	40	–	–	
		$I_C = 1\text{A}, V_{CE} = 2\text{V}$	8	–	80	
		$I_C = 1\text{A}, V_{CE} = 10\text{V}$	25	–	100	
Collector–Emitter Saturation Voltage NTE38	$V_{CE(sat)}$	$I_C = 1\text{A}, I_B = 125\text{mA}$	–	–	2.0	V
NTE175			–	–	0.75	V
Base–Emitter Saturation Voltage NTE38	$V_{BE(sat)}$	$I_C = 1\text{A}, I_B = 125\text{mA}$	–	–	1.4	V
NTE175		$I_C = 1\text{A}, I_B = 100\text{mA}$	–	–	1.4	V
Base–Emitter ON Voltage NTE175 Only	$V_{BE(on)}$	$I_C = 1\text{A}, V_{CE} = 10\text{V}$	–	–	1.4	V
Dynamic Characteristics						
Current Gain –Bandwidth Product NTE38	f_T	$I_C = 200\text{mA}, V_{CE} = 10\text{V}, f_{test} = 5\text{MHz},$ Note 3	20	–	–	MHz
NTE175			15	–	–	MHz
Output Capacitance (NTE175 Only)	C_{ob}	$V_{CB} = 10\text{V}, I_E = 0, f = 1\text{MHz}$	–	–	120	pF

Note 2. Pulse Test: Pulse Width $\leq 300\mu\text{s}$, Duty Cycle $\leq 2\%$.

Note 3. $f_T = |h_{fe}| \bullet f_{test}$

Electrical Characteristics (Cont'd): ($T_C = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit	
Second Breakdown							
Second Breakdown Collector Current NTE38	I _{S/b}	t = 1s (Non–Repetitive), V _{CE} = 40V	875	–	–	mA	
NTE175		V _{CE} = 100V	350	–	–	mA	
Switching Characteristics							
NTE38							
Rise Time	t _r	V _{CC} = 200V, I _C = 1A I _{B1} = I _{B2} = 125mA	–	–	0.6	μs	
Storage Time	t _s		–	–	2.5	μs	
Fall Time	t _f		–	–	0.6	μs	
NTE175							
Rise Time	t _r	V _{CC} = 200V, I _C = 1A	I _{B1} = 100mA, R _L = 200Ω	–	–	3.0	μs
Storage Time	t _s			–	–	4.0	μs
Fall Time	t _f			–	–	3.0	μs

