




NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION: NOT REQUIRED
4. PACKAGING: NOT REQUIRED
5. MATES WITH: NONE
6. "XX" REFERS TO THE QUANTITY OF CIRCUITS.
7. -58 OPTION: DO NOT SUPPLY SCREWS.
8. INCH DIMENSIONS ARE SHOWN IN BRACKETS [LXXX].
9. ALL COMPONENTS ARE ROHS COMPLIANT.

4	XX*2	SCREW, #10-32, DOG PNT, PHIL-SLOT	BRASS	NICKEL
3	XX	RIVET, SEMI-TUBE	BRASS	ZN, CLEAR CHROMATE
2	XX	TERMINAL, EYELET, TWIN	BRASS	BRIGHT NICKEL
1	1	INSULATOR, DR, AS MOLDED	PHENOLIC	BLACK
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH

ADDED -58 OPTION EC NO: ETC2006-0510 DRWN:HEILE 2006/06/22 CHKD:RDEROSS 2006/07/13 APPR: JMACNEIL 2006/07/13	DESCRIPTION	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
			mm INCH		DRAWN BY R. KEMP	DATE 2003/05/09	TITLE 17.46MM [.688] DR BTS, PHENOLIC ASSY					
			4 PLACES ± --- ±.0015		CHECKED BY R. STONE	DATE 2003/05/12						
			3 PLACES ±0.038 ±.005		APPROVED BY P. WALTZ		DATE 2003/05/13		MOLEX MOLEX INCORPORATED			
			2 PLACES ±0.13 ±.01									
			1 PLACE ±0.3 ±---									
			ANGULAR ± 2 °									
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.			SHEET NO.	
						SEE CHART		SD-38280-001			1 OF 1	
REV			SIZE B			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						