

D
Dimensioning and tolerancing per ASME Y14.5M-2009

B

A

D
C

B


A

4		3		2		1	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST	
© COPYRIGHT		ALL RIGHTS RESERVED.					
				REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	C2	ECR-13-003301		21FEB2013	XZ	SX	

REPLACED BY OCEAN STYLE APPLICATOR PART NUMBER 2151202-1

FOR REPLACEMENT PARTS FOR APPLICATOR 1530007
REFER TO ADDITIONAL PAGE(S). SPARE PARTS KIT (IF LISTED)
WILL REMAIN AVAILABLE.

THE REPLACEMENT OCEAN STYLE APPLICATOR HAS THE
SAME TERMINATOR/PRESS INTERFACE AS APPLICATOR
1530007

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN X. ZHAO		 TE Connectivity	
		CHK S. XI			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ±		PRODUCT SPEC	
		1 PLC ±		APPLICATION SPEC	
		2 PLC ±		SIZE	
		3 PLC ±		CAGE CODE	
4 PLC ±		4 PLC ±		DRAWING NO	
MATERIAL		FINISH		RESTRICTED TO	
				C- 1530007	
				SCALE	
				SHEET 1 OF 2	
				REV C2	

 1. RECOMMENDED SPARE PARTS.

2. GREASE RAM, CAM, CAM FOLLOWER AND FEED ROD LIGHTLY.


3. LUBRICATE DAILY PER THE APPLICATOR INSTRUCTION SHEET SUPPLIED WITH THE APPLICATOR.

 4. INSULATION RANGE 1.49–2.39 [.059–.094 IN] OR (2) X 1.70 [.067 IN] MAX.

 5. CUT TO LENGTH AT ASSEMBLY.



ON INSTALLATION, SET WIRE
DISC TO LARGEST WIRE SIZE
SETTING. USE OF SETTINGS
BELOW MIN REQUIRED CRIMP
HEIGHT SETTING WILL CAUSE
DAMAGE TO CRIMP TOOLING.



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN B. HIGMAN		150C104		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWG —		NAME	
		0 PL/C ± —		APVD TELBEN 150C104		FINE ADJ SIDE FD HD-I APPL	
		1 PL/C ± —		PRODUCT SPEC		—	
		2 PL/C ± —		—		—	
		3 PL/C ± —		APPLICATION SPEC		—	
4 PL/C ± —		6 PL/C ± —		SIZE		CAGE CODE	
ANGLES FINISH ± —		WEIGHT —		DRAWING NO		RESTRICTED TO	
MATERIAL —		—		A1 00779		C=1530007	
		CUSTOMER DRAWING		SCALE —		SHEET 1 OF 1	
						REV C	