


35203MOJT Product Details

[!\[\]\(faf942dc3e59ce8eb64b4ac481eca7e0_img.jpg\) Share](#) [!\[\]\(f6b0299e0b5e4340e509b71914970da0_img.jpg\) Print](#) [!\[\]\(b5153706f6ea2fc2c42e8803b6804d18_img.jpg\) Email](#)**35203MOJT**

(6-1879005-5)

TE Internal Number: 6-1879005-5

[!\[\]\(4f6bf54ae7e4144a72d78316053e412d_img.jpg\) View 3D PDF](#)

Fixed Resistors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Fixed Resistor
- Resistor Type = Power Resistor
- Resistance Selection = M Ω
- Resistance = 3M Ω
- Power Rating = 1.00 W

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[!\[\]\(4186b6ce3a1c83eabb297c1bfd00309c_img.jpg\) Add to My Part List](#) [!\[\]\(47d65e2db8884b900589700f5ce09b80_img.jpg\) Request Sample](#) [!\[\]\(892988f7fe1371795b60ed02c05cbe5c_img.jpg\) Find Similar Products](#) [!\[\]\(26ee6c9e20d493af7ace2d63129d379b_img.jpg\) Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [SMD POWER RESISTOR SERIES 3520](#) (PDF, English)

Additional Information:

- [Product Line Information](#)

Catalog Pages/Data Sheets:

- [1309350 PASSIVE COMPONENT](#) (PDF, English)
- [SMD Power Resistors - Type 3520 Series - Tyco Electr...](#) (PDF, English)

Related Products:

- [Tooling](#)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version BA)
- [3D Model](#) (IGES, Version BA)
- [3D Model](#) (STEP, Version BA)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Fixed Resistor
- Resistor Type = Power Resistor
- [Element](#) = Thick Film
- [Series](#) = 3520
- Termination Type = Solder

Configuration Features:

- [Number of Terminations](#) = 2
- [Number of Resistors](#) = 1

Electrical Characteristics:

- [Resistance Selection \(\$\Omega\$ \)](#) = M
- [Resistance \(\$\Omega\$ \)](#) = 3M
- [Power Rating \(W\)](#) = 1.00
- [Tolerance \(%\)](#) = 5
- [Package Type](#) = Taped and Reeled

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Body Features:

- [Mount Style](#) = Surface Mount
- [Packaging Style](#) = 2512
- [Package, Component Size](#) = 6.4 x 3.2

Conditions for Usage:

- [Temperature Coefficient \(ppm/ \$^{\circ}\$ C\)](#) = ± 200

Operation/Application:

- [Application](#) = Power

Other:

- Brand = CGS

Corporate Information

[Who We Are](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)

Quick Links

[Check Distributor Inventory](#)[Cross Reference](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)

Customer Support

[Email or Chat With Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

