


SERIES**4590R
4590****High Current Filter Inductors**

Actual Size (Max.)

**Physical Parameters**

	Inches	Millimeters
Length	0.900 Max.	22.86 Max.
Diameter	0.455 Max.	11.55 Max.
Lead Size		
AWG #20 TCW	0.032 ± 0.002	0.813 ± 0.05
Lead Length	1.10 Min.	27.94 Min.

Operating Temperature

-55°C to +125°C

-55°C to +85°C @ full rated current

Current Rating at 85°C Ambient 40°C Rise**Maximum Power Dissipation at 85°C** 0.70 W**Dielectric Withstanding Voltage** 2500 V RMS**Incremental Current** The current which will decrease the inductance by approximately 5%.**Inductance Measurement** Inductance is measured @ 1 kHz with 1 VAC open circuit and 0 dc bias.**Inductance Tolerance** Tolerance is specified by suffixing an alpha character to the part number as follows: J = 5%, K = 10%, and L = 15%. Units are normally supplied to the tolerance indicated in table.**High Saturation Bobbin** allows for high inductance with low DCR.**High Resistivity** Core offers very high parallel resistance, resulting in maximum coil performance.**4590 Marking** DELEVAN; inductance; tolerance.**4590R Marking** DELEVAN; 4590R; dash number with tolerance letter.

Example: 4590-393K

 DELEVAN
 39 uH
 ±10%

Example: 4590R-393K

 DELEVAN
 4590R
 393K
Packaging Bulk only
 DASH NUMBER*
 NOMINAL INDUCTANCE
 (μH) ±10%
 DC RESISTANCE
 MAXIMUM (OHMS)
 CURRENT RATING
 MAXIMUM (AMPS)
 CURRENT DC (AMPS)
 INCREMENTAL
SERIES 4590 FERRITE CORE

-392K	3.9	0.007	9.75	8.2
-472K	4.7	0.008	9.11	7.5
-562K	5.6	0.011	7.77	6.9
-682K	6.8	0.011	7.60	6.3
-822K	8.2	0.013	7.15	5.7
-103K	10.0	0.016	6.44	5.2
-123K	12.0	0.018	6.07	4.7
-153K	15.0	0.020	5.76	4.3
-183K	18.0	0.022	5.49	3.9
-223K	22.0	0.024	5.26	3.5
-273K	27.0	0.025	5.15	3.2
-333K	33.0	0.028	4.87	2.9
-393K	39.0	0.031	4.63	2.7
-473K	47.0	0.034	4.45	2.5
-563K	56.0	0.043	3.93	2.3
-683K	68.0	0.059	3.355	2.1
-823K	82.0	0.066	3.175	1.9
-104K	100	0.084	2.815	1.7
-124K	120	0.113	2.43	1.6
-154K	150	0.129	2.27	1.4
-184K	180	0.150	2.105	1.3
-224K	220	0.162	2.025	1.2
-274K	270	0.226	1.715	1.1
-334K	330	0.257	1.61	0.95
-394K	390	0.288	1.52	0.88
-474K	470	0.393	1.30	0.80
-564K	560	0.504	1.15	0.74
-684K	680	0.570	1.08	0.67
-824K	820	0.643	1.015	0.61
-105K	1000	0.844	0.89	0.56
-125K	1200	0.977	0.825	0.51
-155K	1500	1.18	0.75	0.46
-185K	1800	1.50	0.665	0.42
-225K	2200	1.76	0.615	0.38
-275K	2700	2.13	0.56	0.34
-335K	3300	2.53	0.51	0.31
-395K	3900	2.84	0.48	0.29
-475K	4700	3.79	0.415	0.26
-565K	5600	4.24	0.395	0.24
-685K	6800	5.75	0.34	0.22
-825K	8200	6.44	0.32	0.20
-106K	10000	7.30	0.30	0.18
-126K	12000	9.34	0.265	0.17
-156K	15000	10.7	0.25	0.15
-186K	18000	14.8	0.21	0.14
-226K	22000	18.0	0.19	0.12
-276K	27000	22.7	0.17	0.11
-336K	33000	25.7	0.16	0.10
-396K	39000	29.7	0.15	0.09
-476K	47000	33.7	0.14	0.09
-566K	56000	38.0	0.13	0.08
-686K	68000	52.8	0.11	0.07
-826K	82000	67.3	0.10	0.07
-107K	100000	76.0	0.09	0.06

Optional Tolerances: J = 5% L = 15%

*Complete part # must include series # PLUS the dash #

For surface finish information, refer to www.delevanfinishes.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

API Delevan:

[4590R-276K](#) [4590R-274K](#) [4590R-273K](#) [4590R-275K](#) [4590R-225K](#) [4590R-223K](#) [4590R-226K](#) [4590R-224K](#)
[4590R-682K](#) [4590R-686K](#) [4590R-684K](#) [4590R-683K](#) [4590R-685K](#) [4590R-395K](#) [4590R-393K](#) [4590R-396K](#) [4590R-392K](#) [4590R-394K](#) [4590R-336K](#) [4590R-334K](#) [4590R-333K](#) [4590R-335K](#) [4590R-153K](#) [4590R-155K](#) [4590R-154K](#)
[4590R-156K](#) [4590R-825K](#) [4590R-823K](#) [4590R-822K](#) [4590R-826K](#) [4590R-824K](#) [4590-224K](#) [4590-824K](#) [4590-125K](#)
[4590-226K](#) [4590-394K](#) [4590-153K](#) [4590-563K](#) [4590-107K](#) [4590-156K](#) [4590-275K](#) [4590-565K](#) [4590-683K](#) [4590-124K](#) [4590-472K](#) [4590-826K](#) [4590-333K](#) [4590-184K](#) [4590-685K](#) [4590-105K](#) [4590-186K](#) [4590-335K](#) [4590-104K](#)
[4590-474K](#) [4590-392J](#) [4590-472J](#) [4590-562J](#) [4590-682J](#) [4590-822J](#) [4590-103J](#) [4590-123J](#) [4590-153J](#) [4590-183J](#)
[4590-223J](#) [4590-273J](#) [4590-333J](#) [4590-393J](#) [4590-473J](#) [4590-563J](#) [4590-683J](#) [4590-823J](#) [4590-104J](#) [4590-124J](#)
[4590-154J](#) [4590-184J](#) [4590-224J](#) [4590-274J](#) [4590-334J](#) [4590-394J](#) [4590-474J](#) [4590-564J](#) [4590-684J](#) [4590-824J](#)
[4590-105J](#) [4590-125J](#) [4590-155J](#) [4590-185J](#) [4590-225J](#) [4590-275J](#) [4590-335J](#) [4590-395J](#) [4590-475J](#) [4590-565J](#)
[4590-685J](#) [4590-825J](#) [4590-106J](#) [4590-126J](#) [4590-156J](#) [4590-186J](#) [4590-226J](#)