


SCALE 5.000

5.PACKAGE SPEC: GS-14-1420

6

PART NO.	PDS.	DIM"x"	DIM"x"
20021111-XXX92XXLF	2 X 46	58.42	57.15
20021111-XXX94XXLF	2 X 47	59.69	58.42
20021111-XXX96XXLF	2 X 48	60.96	59.69
20021111-XXX98XXLF	2 X 49	62.23	60.96
20021111-XXXA0XXLF	2 X 50	63.50	62.23

20021111 - X X X XX X X LF

—LEAD FREE

—PLATING OPTIONAL

1: GOLD FLASH AT CONTACT, 1.27 μ m MIN. MATTE TIN AT TAIL

2: GOLD FLASH AT CONTACT, GOLD FLASH AT TAIL

4: 0.25um Au MIN. AT CONTACT, 1.27um MIN.MATTE TIN AT TAIL

5: 0.25um Au MIN. AT CONTACT, GOLD FLASH AT TAIL

6: 0.38um GXT MIN. AT CONTACT, 1.27um MIN.MATTE TI

7: 0.38um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL

8: 0.76um GXT MIN. AT CONTACT, 1.27um MIN. MATTE TI

9: 0.76um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL

—PACKING STYLE

—PACKING STYLE
T. TUBE

Q: TAPE

—PIN NO. SEE TABLE

-FIN NO. SEE TABLE
 MATING LENGTHS

—MATING LENGTH(DIM'A')

0: 3.05MM

—TAIL LENGTH(DIM'B')

0: 2.30MM (FOR 1.6MM PCB)

1: 1.60MM (FOR 1.0MM PCB)

2: 2.70MM (FOR 2.0MM PCB)

—RESERVE CODE

—RESERVE CDD
0: STANDARD

mat'l. code					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MINITEK127®					
ltr	ecn	no	dr	date	tolerances unless otherwise specified		.0±.30		 mm		title UNSHROUDED HDR VT TH					
					angles		.00±.20									
					linear		.000±.10									
					0±2°				scale 1:1							
					dr		ZK HU		09/28/12		dwg no 20021111 sheet2 of 2 A3					
					engr		ZK HU		09/28/12							
					chr		BIAN RICK		09/28/12							
					appd		BIAN RICK		09/28/12							
sheet index		revision sheet		G 1	G 2							type Product Customer Drawing				