

Silicon Avalanche Diodes

1500 Watt Axial Leaded Transient Voltage Suppressors

ICTE/MPTE Series



The ICTE/MPTE series 1500 W transient suppressors are designed specifically for protection of CMOS, NMOS, BiMOS, and other integrated circuits available today for TTL, DTL, ECL, RTL, and linear functions. This series offers the lowest clamping voltages.

FEATURES

- Stand-off voltage range 5 to 45 Volts
- Uni-directional and Bi-directional
- Glass passivated junction
- Very low clamping voltages
- 100% surge tested

MAXIMUM RATING



- Peak Pulse Power (Ppk): 1500 Watts (10 x 1000µs) @25°C (see diagram on page 3 for wave form)
- 5 watt steady state
- Response time: 1×10^{-12} seconds (theoretical)
- Forward surge rating 200 Amps, 8.3ms half sine wave, (uni-directional devices only)
- Operating & storage temperature: -55°C to +150°C

MECHANICAL CHARACTERISTICS


- Case: DO-201AD: Molded plastic over glass passivated junction
- Terminals: Axial leads, solderable per MIL-STD-202 Method 208
- Solderable leads = 230°C for 10 seconds (1.59mm from case)
- Marking: cathode band, (positive terminal, uni-directional devices only), device code, logo
- Weight: 1.5 grammes (approx)

Agency Approvals: Recognized under the Components Program of Underwriters Laboratories.

Agency File Number: E128662



ORDERING INFORMATION



B = Bulk (500 pcs)

T = Tape and reeled (1500 pcs)

Silicon Avalanche Diodes

1500 Watt Axial Leaded Transient Voltage Suppressors

ICTE/MPTE Series




Figure 1 - Typical Junction Capacitance




Figure 2 - Peak Pulse Power Rating Curve

ELECTRICAL SPECIFICATION @ Tamb 25°C

Part Number	Reverse Standoff Voltage Vr (Volts)	Minimum Breakdown Voltage Vbr @1mA (Volts)	Maximum Reverse Leakage Ir @ Vr (μA)	Maximum Clamping Voltage Vc @ IPP 1=1A (Volts)	Maximum Clamping Voltage Vc @ IPP 2=10A (Volts)	Maximum Peak Pulse Current IPP (A)
ICTE-5/MPTE-5*	5.0	6.0	300.0	7.1	7.5	160.0
ICTE-8/MPTE-8*	8.0	9.4	25.0	11.3	11.5	100.0
ICTE-10/MPTE-10	10.0	11.7	2.0	13.7	14.1	90.0
ICTE-12/MPTE-12	12.0	14.1	2.0	16.1	16.5	70.0
ICTE-15/MPTE-15	15.0	17.6	2.0	20.1	20.6	60.0
ICTE-18/MPTE-18*	18.0	21.2	2.0	24.2	25.2	50.0
ICTE-22/MPTE-22	22.0	25.9	2.0	29.8	32.0	40.0
ICTE-36/MPTE-36	36.0	42.4	2.0	50.6	54.3	23.0
ICTE-45/MPTE-45	45.0	52.9	2.0	63.3	70.0	19.0
ICTE-8C/MPTE-8C	8.0	9.4	50.0	11.4	11.6	100.0
ICTE-10C/MPTE-10C	10.0	11.7	2.0	14.1	14.5	90.0
ICTE-12C/MPTE-12C	12.0	14.1	2.0	16.7	17.1	70.0
ICTE-15C/MPTE-15C	15.0	17.6	2.0	20.8	21.4	60.0
ICTE-18C/MPTE-18C	18.0	21.2	2.0	24.8	25.5	50.0
ICTE-22C/MPTE-22C	22.0	25.9	2.0	30.8	32.0	40.0
ICTE-36C/MPTE-36C	36.0	42.4	2.0	50.6	54.3	23.0
ICTE-45C/MPTE-45C	45.0	52.9	2.0	63.3	70.0	19.0

ICTE-5 is not available in Bi-directional. Suffix 'C' denotes Bi-directional device. * Preferred voltages.

Vf max = 3.5 Volts max at If = 50A 300μS square wave pulse

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[ICTE-10](#) [ICTE-10C](#) [ICTE-12](#) [ICTE-12C](#) [ICTE-15](#) [ICTE-15C](#) [ICTE-18](#) [ICTE-18C](#) [ICTE-22](#) [ICTE-22C](#) [ICTE-36](#)
[ICTE-36C](#) [ICTE-45](#) [ICTE-45C](#) [ICTE-5](#) [ICTE-8](#) [ICTE-8C](#) [MPTE-10 \(1N6375\)](#) [MPTE-10C \(1N6383\)](#) [MPTE-12](#)
[\(1N6376\)](#) [MPTE-12C \(1N6384\)](#) [MPTE-15 \(1N6377\)](#) [MPTE-15C \(1N6385\)](#) [MPTE-18 \(1N6378\)](#) [MPTE-18C \(1N6386\)](#)
[MPTE-22 \(1N6379\)](#) [MPTE-22C \(1N6387\)](#) [MPTE-36 \(1N6380\)](#) [MPTE-36C \(1N6388\)](#) [MPTE-45 \(1N6381\)](#) [MPTE-45C](#)
[\(1N6389\)](#) [MPTE-5 \(1N6373\)](#) [MPTE-8 \(1N6374\)](#) [MPTE-8C \(1N6382\)](#)