





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		H4	REVISED PER ECR-16-000306	12JAN2016	NK	DC


- 1 WIRE RANGE: 0.3–0.82mm² (22–18 AWG)
- 2 INSULATION RANGE: 1.50 – 3.10 DIA.
- 3 FINISH: 0.76μm MINIMUM GOLD IN LOCALIZED GOLD PLATE AREA OVER 1.27μm MINIMUM NICKEL.
- 4 FINISH: 2.54μm MINIMUM PRE-TIN IN LOCALIZED TIN PLATE AREA.
- 5 FINISH: 2.54μm MINIMUM PRE-TIN ALL OVER.



SECTION A–A



SECTION B–B



SECTION C–C

GOLD 3 4	PHOS. BRZ.	794955–4
PRE-TIN 5	PHOS. BRZ.	794955–3
GOLD 3 4	BRASS	794955–2
PRE-TIN 5	BRASS	794955–1
FINISH	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HAMM 07-SEP-2001	 TE Connectivity			
		CHK D. COLEY 07-SEP-2001				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. COLEY 07-SEP-2001	NAME			
	0 PLC ±	PRODUCT SPEC	TERMINAL PIN			
	1 PLC ± 0.25 [.010]	108-2112	VAL-U-LOK(TM)			
	2 PLC ± 0.15 [.006]					
	3 PLC ± -	APPLICATION SPEC				
	4 PLC ±	114-13172	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL	FINISH	WEIGHT	A2	00779	C=794955	—
			CUSTOMER DRAWING		SCALE 10:1	SHEET 1 of 1
					REV H4	