


OGA DIAGONAL: 11.62 [295.18]
VA DIAGONAL: 10.84 [275.46]
PA DIAGONAL: 10.25 [260.26]




(SER)
EXII-7720SC
98-0003-2217-6
SERIAL CONTROLLER
SOLDER SIDE

PIN #1
±.060 [1.52]


(USB R)
EXII-7760UC
98-0003-2814-0
USB CONTROLLER
SOLDER SIDE

PIN #1
±.060 [1.52]




(FFC)
SEE NOTE 2

PIN #1
±.060 [1.52]



.147 ±.020 [3.73 ±.51]
TOTAL THICKNESS
OF GLASS, CABLE
AND STRAIN RELIEF



SECTION A-A
SCALE: NONE

- NOTES:
1. WEIGHT OF GLASS IN GRAMS: 32.1 ±10%
 2. NICOMATIC HOUSING P/N: 0L05
 3. NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
 4. HOUSING ORIENTED WITH LATCH DOWN

TOP LEVEL NUMBER	US NUMBER	TYPE	DM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-8021-203	98-0003-2503-9	FFC	4.27" [108.46]	AG500	23655
17-8021-205	98-0003-2504-7	FFC	8.00" [203.20]	AG500	23655
17-8021-206	98-0003-2505-4	NOV	SEE DWG	AG500	23655
17-8021-221	98-0003-2507-0	SFR	4.27" [108.46]	AG500	23655
17-8021-227	98-0003-2510-4	SFR	8.00" [203.20]	AG500	23655
17-8021-218	98-0003-2916-3	USB R	4.27" [108.46]	AG500	23655
17-8021-226	98-0003-2509-6	USB R	8.00" [203.20]	AG500	23655

PINOUT
1 LR
2 LL
3 SHED
4 UL
5 UR

UNITS	INCHES [MM]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
X	±.03 [1.76]
.XX	±.015 [1.38]
XXX	±.015 [1.38]
ANGLES	±1°

3M TOUCH SYSTEMS 3M TOUCH, WA USA	THIS DOCUMENT IS THE PROPERTY OF 3M. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED HEREIN. IT IS NOT TO BE REPRODUCED OR USED FOR ANY OTHER PURPOSES WITHOUT THE WRITTEN PERMISSION OF 3M.
---	---

MARKETING DRAWING SCT32NN 10.84"

DO NOT SCALE DRAWING	SCALE 1 = 1
DRAWN K. CROWLEY	9/05
SIZE C	DOCUMENT NO. 28209-MKT
SHEET 1 OF 1	REV H