



All dimensions are in mm; tolerances according to ISO 2768 c-H

Available variants

Type	"A" (mm)	"C" (mm)	Insertion loss ≤ (dB) at 26.5 GHz	Marking	Weight (g) / pce
LU7-153-500	500	20±3	1.30	ROSENBERGER WW/YY XXX LU7-153-500	58
LU7-153-1000	1000	20±3	2.30	ROSENBERGER WW/YY XXX LU7-153-1000	94
LU7-153-1500	1500	20±3	3.35	ROSENBERGER WW/YY XXX LU7-153-1500	130
LU7-153-2000	2000	20±3	4.40	ROSENBERGER WW/YY XXX LU7-153-2000	166

WW - week

YY - year

XXX – serial no.

Documents

Technical data sheet connectors

RPC-3.50 plug

03S121-2U7S3

RPC-3.50 jack

03K121-2U7S3

Technical data sheet cable

RTK 162

Assembly parts

Connector left

RPC-3.50 plug

03S121-2U7S3

Connector right

RPC-3.50 jack

03S121-2U7S3

Cable

RTK 162

Technical Data Sheet

Rosenberger

Cable assembly - Standardportfolio
RPC-3.50 Plug / RPC-3.50 Jack – RTK 162

LU7-153-XXX

Electrical data

Impedance	50 Ω
Frequency	DC to 26.5 GHz
Return loss	≥ 19 dB, DC to 26.5 GHz
Insertion loss	see table available variants
RF-leakage	≥ 100 dB up to 1 GHz

Mechanical data

Minimum bend radius:	
Single	9.65 mm
Multiple	50.8 mm

Environmental data

Temperature range	-40°C to +85°C
2002/95/EC (RoHS)	compliant

Packing

Standard	1 pce in box
----------	--------------

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Martin Moder	26/01/12	Herbert Babinger	03/02/12	g00	12-s045	Maik Knoll	03/02/12
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Fax : +49 8684 18-499 Email : info@rosenberger.de			Page 2 / 2