



6374645
THIS DRAWING IS A CONTROLLED DOCUMENT

Restricted to: General Release

USED ON



Left Side
Connector(s): MT-RJ (No Pins)
Mode: SM
Housing Color: Black
Geom. Spec: 115-1215



Fiber Path
Fiber A - - - - - B
Fiber B - - - - - A

Right Side
Connector(s): LC-Duplex
Mode: SM
Housing Color: Blue
Geom. Spec: N/A

- Notes:
- 1 IL and RL tested at 1310nm.
 - 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
 - 3 Label 2 will not be present on any cable assembly less than 5 meters long.
 - 4 Includes dust caps (not shown on print).

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

	B	Rev Per EC#	06-022379	9/29/2006	-	MK			
P	LTR	REVISION RECORD	DATE	DATE	DATE	DATE	DATE	DATE	DATE

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
meters	0 PLC ± .
	1 PLC ± .
	2 PLC ± .
	3 PLC ± .
	4 PLC ± .

DIN	Cable Assy Configurator	MATERIAL	HEAT TREAT
OK	Michael Kepko		
APVD	Michael Kepko		
NAME	FO C/A - 2 fiber, SM, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex		
SCALE	NTS	SIZE	A2
DRAWING NO	C- 6374645		SHEET
1 of 3			REV B

Customer Print

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

THIS DRAWING IS A CONTROLLED DOCUMENT.
PAGE NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Restricted to: General Release

USED ON

Part #	L (meters)	L (feet)	MT-RJ (No Pins), Black		LC-Duplex, Blue	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-6374645-1	0.950 - 1.050	3.11 - 3.44	0.5	26	0.35	45
0-6374645-2	1.950 - 2.050	6.39 - 6.72	0.5	26	0.35	45
0-6374645-3	2.950 - 3.050	9.67 - 10.00	0.5	26	0.35	45
0-6374645-4	3.920 - 4.080	12.86 - 13.38	0.5	26	0.35	45
0-6374645-5	4.920 - 5.080	16.14 - 16.66	0.5	26	0.35	45
0-6374645-6	5.920 - 6.080	19.42 - 19.94	0.5	26	0.35	45
0-6374645-7	6.920 - 7.080	22.70 - 23.22	0.5	26	0.35	45
0-6374645-8	7.920 - 8.080	25.98 - 26.50	0.51	26	0.36	45
0-6374645-9	8.850 - 9.150	29.03 - 30.01	0.51	26	0.36	45
1-6374645-0	9.850 - 10.150	32.31 - 33.30	0.51	26	0.36	45
1-6374645-1	10.850 - 11.150	35.59 - 36.58	0.51	26	0.36	45
1-6374645-2	11.850 - 12.150	38.87 - 39.86	0.51	26	0.36	45
1-6374645-3	12.850 - 13.150	42.15 - 43.14	0.51	26	0.36	45
1-6374645-4	13.850 - 14.150	45.43 - 46.42	0.51	26	0.36	45
1-6374645-5	14.850 - 15.150	48.72 - 49.70	0.51	26	0.36	45
1-6374645-6	15.840 - 16.160	51.96 - 53.01	0.51	26	0.36	45
1-6374645-7	16.830 - 17.170	55.21 - 56.33	0.51	26	0.36	45
1-6374645-8	17.820 - 18.180	58.46 - 59.64	0.51	26	0.36	45
1-6374645-9	18.810 - 19.190	61.71 - 62.95	0.51	26	0.36	45
2-6374645-0	19.800 - 20.200	64.96 - 66.27	0.51	26	0.36	45
2-6374645-1	20.790 - 21.210	68.20 - 69.58	0.51	26	0.36	45
2-6374645-2	21.780 - 22.220	71.45 - 72.90	0.52	26	0.37	45
2-6374645-3	22.770 - 23.230	74.70 - 76.21	0.52	26	0.37	45
2-6374645-4	23.760 - 24.240	77.95 - 79.52	0.52	26	0.37	45
2-6374645-5	24.750 - 25.250	81.20 - 82.84	0.52	26	0.37	45
2-6374645-6	25.740 - 26.260	84.44 - 86.15	0.52	26	0.37	45
2-6374645-7	26.730 - 27.270	87.69 - 89.46	0.52	26	0.37	45
2-6374645-8	27.720 - 28.280	90.94 - 92.78	0.52	26	0.37	45
2-6374645-9	28.710 - 29.290	94.19 - 96.09	0.52	26	0.37	45
3-6374645-0	29.700 - 30.300	97.44 - 99.40	0.52	26	0.37	45
3-6374645-1	30.690 - 31.310	100.68 - 102.72	0.52	26	0.37	45
3-6374645-2	31.680 - 32.320	103.93 - 106.03	0.52	26	0.37	45
3-6374645-3	32.670 - 33.330	107.18 - 109.35	0.52	26	0.37	45
3-6374645-4	33.660 - 34.340	110.43 - 112.66	0.52	26	0.37	45
3-6374645-5	34.650 - 35.350	113.68 - 115.97	0.52	26	0.37	45
3-6374645-6	35.640 - 36.360	116.92 - 119.29	0.53	26	0.38	45
3-6374645-7	36.630 - 37.370	120.17 - 122.60	0.53	26	0.38	45
3-6374645-8	37.620 - 38.380	123.42 - 125.91	0.53	26	0.38	45
3-6374645-9	38.610 - 39.390	126.67 - 129.23	0.53	26	0.38	45
4-6374645-0	39.600 - 40.400	129.92 - 132.54	0.53	26	0.38	45
5-6374645-0	49.500 - 50.500	162.40 - 165.68	0.54	26	0.39	45

Qty	U of M	Description	Item No.
1	piece	HOUSING, CONN, MT-RJ.BLACK	1
1	piece	DUST COVER, MT-RJ	2
1	piece	SPRING, MT-RJ, 3.8 DESIGN	3
1	piece	PIN KEEPER, 3.8MM	4
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	5
1	piece	CRIMP EYELET, MT-RJ	6
2	piece	LC, SC, FC Straight Boot, Blue	7
1	piece	LC Duplex clip, black	8
2	piece	LC Connector Assy, SM	9
1	piece	MT-RJ FERRULE, THERMOPLAST SM	10
AR	meter	2 fiber, SM, 1.8 mm, Twinzip, Yellow, OFNR (Riser)	11
1	piece	MT-RJ TwinZip Bend Limiting Boot, Blue	12
2	piece	Eyelet/Shrink tube assembly - Yellow	13
2	piece	Trace Label	14

B	Rev Per EC#	06-022379	9/29/2006	-	MK		
P	LTR	REVISION RECORD	DATE	DIN	APVD		

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 P.L.C. ± - 1 P.L.C. ± - 2 P.L.C. ± - 3 P.L.C. ± - 4 P.L.C. ± -
Customer Print	

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK Michael Kepko				
APVD Michael Kepko				
NAME FO C/A - 2 fiber, SM, OFNR (Riser) jacket, MT-RJ (No Pins) to LC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 6374645	SHEET 2 of 3	REV B

8 7 6 5 4 3 2 1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

1