





G2G097 Series Centrifugal Blower

Ø 97mm


- DC single inlet, forward curved centrifugal blower. Reverse polarity and locked-rotor protection.
- Housing and impeller made of galvanised sheet-steel. Forward curved impellers are directly press-fitted onto the rotor of the external-rotor motor.
- Direction of rotation is CW as seen from inlet side.
- The external-rotor EC motor integrated in the impeller is mounted to the sidewall of the scroll housing.
- UL, CSA, VDE approvals on some models, please contact application engineering.

Part Number	Curve	CFM @ 0	VDC	Volt. Range	Power (W)	dba	Max Amb. Temp C	Bearing Type	Features	Wgt. (lbs)
G2G097-AA26-09	2	50	12	8 to 14	17	57	65	Ball	No Flange	2.00
G2G097-AA16-01	2	50	24	16 to 28	18	57	65	Ball	No Flange	2.00
G2G097-AA22-50	2	50	48	36 to 56	19	58	65	Ball	No Flange	2.00



DIMENSIONS - inches (mm)

PART NUMBER	A	B	C	D	E	F	G	H	I	J	K	L	M	N	O	P	Q
G2G097	5.63 (143)	5.39 (137)	2.95 (75)	2.44 (62)	-	-	-	-	1.57 (40)	1.81 (46)	1.57 (40)	1.61 (41)	M4	-	3.15 (80)	3.78 (96)	17.72 (450)



ebmpapst

e-mail: sales@us.ebmpapst.com • TEL: 860-674-1515 • FAX: 860-674-8536

ebm-papst Inc., 100 Hyde Road, Farmington, CT 06034 USA

ebm-papst Inc., 2004 © ebm-papst Inc. reserves the right to change any specifications or data without notice