

- ▼ Cable Ties
- [18-30 lb Tensile Strength](#)
- [40-50 lb Tensile Strength](#)
- [Heavy Duty Strength](#)
- [Heavy Duty Wide Strap](#)
- [Q Ties](#)
- [Releasable](#)
- [Releasable Heavy Duty](#)
- [Clamp Ties](#)
- [Double Head](#)
- [Identification](#)
- [Outside Serrated](#)
- [Stainless Steel - 304](#)
- [Stainless Steel - 316](#)
- [High Temp Applications](#)
- [Automatic Tool Cable Ties](#)
- [Swivel Clip Cable Tie](#)
- [Wire Harness Branch Ties](#)
- [Aerial Support Spacer Ties](#)
- [Releasable Grip Ties](#)
- Cable Ties with Fasteners
- Cable Tie Tools
- Clamps and Clips
- [Heatshrink Moulded Shapes](#)
- Mounts
- Heavy Duty Mounts
- Wire Connectors
- Wiring Duct
- Wiring Protection
- Labels, Printers and Software
- [Pre-Terminated Networking](#)
- Copper Network Solutions
- Fiber Network Solutions
- Jacks and Wall Plates
- Racks - Cable Management
- Surface Raceway Systems

T18R5M4

Standard Cable Tie, 4" Long, 18lb Tensile Strength, PA66, Green, 1000/pkg

Article Number: 111-01855

Part Number: T18R5M4

Type: T18R



→ [Find a Distributor](#)

→ [Order Samples](#)


→ [Get Technical Drawings](#)

 |  Share

→ **Base Data**

Part No.	T18R5M4
Type	T18R
Color	Green (GN)
Features	• Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Application Method	Quick, simple application by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	Used to bundle and secure wire and cable.
Variant	Inside Serrated

→ **Product Dimensions**



Min. Tensile Strength	18.0lbs / 80.0N
Length (L)	4.0" / 100.0mm
Width (W) (imperial)	0.1"
Width (W)	2.45mm
Min. Ø Bundle	0.06" / 1.5mm
Max. Ø Bundle	0.86" / 22.0mm

→ **Material and Specifications**

Material	Polyamide 6.6 (PA66)
----------	----------------------

US MILSPEC	MS3367-4-5
CSA Certified	No
Flammability	UL94 V2
Material Specification	RoHS / HF
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	
Specification	MIL 53421 / UL ZODZ2.E64139
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes

 Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	1000
Carton Qty.	10000
EAN code	4031026425061
UPC	089306069652

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)