



Wiha Insulated Pliers & Cutters

Insulated High Leverage Diagonal Cutters



1000volt

[SHOP](#)

328 High Leverage Diagonal Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E, up to 1000 volt. Individually Tested. DIN ISO 5749

Semi-circular. Low wear lap joint, riveted and able to withstand high levels of load. Lightweight action, clean cutting. Long term cutting is achieved through additional inductive hardening to approx. 64 HRC. C 60 special tool steel hardened and tempered to high quality. For soft, hard and piano wire, lay-on joint, optimized power transmission.

Item No.		mm	Inch	Cutting Capacity Copper AWG		
328 35	Z16016006	160	6.3	#6	1	.54
328 36	Z16018006	180	7.0	#5	1	.57
328 38	Z16020006	200	8.0	#4	1	.64

Insulated Electrician's Diagonal Cutters



1000volt

[SHOP](#)

328 Diagonal Cutters W/Stripping Holes. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E, up to 1000 volt. Individually Tested.

Drop-forged from special tool steel, cutters additionally induction hardened (approx. 60 HRC), chrome-nickel plated, mirror-polished. Ergonomic comfort grip with slip guard. Holes in the cutting edge for stripping copper wire of Ø 1.5 and 2.5. Strips AWG sizes #10 & #14.

Item No.		mm	Inch	Cutting Capacity Copper AWG		
328 61	Z14016006	160	6.3	#6	1	.54

Insulated Cable Cutters



1000volt

[SHOP](#)

328 Cable Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E, up to 1000 volt.

Individually Tested. Drop-forged from durable CV steel, cutters additionally induction hardened, chrome & nickel plated, Mirror-polished. For copper and aluminum cables (not for steel wires), integrated release spring, one-hand locking, adjustable joint, anti-squeeze feature.

Item No.		mm	Inch	Min	Max		
328 46	Z50023006	210	8.3	17	40	1	.98
328 48	Z50017006	170	6.5	10	60	1	.67

Insulated Long Nose Pliers



1000volt

[SHOP](#)

328 Long Nose Pliers With Cutters. Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E,

up to 1000 volt. Individually Tested. Drop-forged from special tool steel, cutters additionally induction hardened (approx. 60 HRC), chrome-nickel plated, mirror-polished, ergonomic comfort grip with slip guard, half-round jaws, serrated gripping surface.

Item No.		mm	Inch	Cutting Capacity Copper AWG		
328 06	Z05016006	160	6.3	#10	1	.32
328 08	Z05020006	200	8.0	#8	1	.42

Use & Care Guide For Insulated Tools:

Store tools to minimize risk of damage to insulation
Inspect insulation prior to each use of any insulated tool
If you doubt the integrity of the insulation destroy the tool or have it retested
Use insulated tools where the ambient temperature is between -20 to +70° C
Have a qualified safety technician inspect and re-certify tools annually for safe use

Warning! Insulated tools are not intended for use on live or energized circuits. Always disconnect and de-energize all equipment & circuits. **NEVER!** work on live or energized circuits or equipment.