





MOLEX PART NO.	ITW RANSBURG PART NO.	LENGTH
849090266	79338-36	36 FT. ±4 IN. [11.0M ±102mm]
849090267	79338-50	50 FT. ±6 IN. [15.2M ±152mm]
849090268	79338-75	75 FT. ±9 IN. [22.8M ±228mm]
849090269	79338-100	100FT. ±12 IN. [30.5M ±305mm]
849090270	79338-150	150 FT. ±12IN. [45.7M ±305mm]

- NOTES:
1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PACKAGING: ASSEMBLIES ARE TO BE BAGGED SEPERATELY
EACH BAG IS TO BE LABELED WITH CUSTOMER PART NO. PER CHART
4. MATES WITH: CUSTOMER SPECIFIC PART
5. CABLE IS CUSTOMER SUPPLIED



10	1	LABEL	MYLAR	BLACK/CHROME
9	1	SEAL	TRI-SEAL F-217	WHITE
8	1	COUPLING RING, EXT.THREAD	BRASS	NICKEL PLATED
7	1	COUPLING RING, INT. THREAD	BRASS	NICKEL PLATED
6	2	OVERMOLD	PUR	BLACK
5	5	CONTACT PIN	Cu ALLOY	GOLD PLATED
4	1	PIN INSULATOR	NYLON	BLACK
3	5	CONTACT SOCKET	Cu ALLOY	GOLD PLATED
2	1	SOCKET INSULATOR, 5/C	NYLON	BLACK
1	1	CABLE, 5X20AWG SHLD.	PUR JACKET	BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

RELEASE TO BUILD EC NO: ETC2006-0111 DRAWN: STONE CHKD: R. DEROSS APPR: R. DEROSS A	2005/12/01 2005/12/02 2005/12/02	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION		
					mm	INCH	DRAWN BY R. STONE	DATE 11/09/05	TITLE MICRO-C EXT. CORD, M/F DC KEY, 5/C			
				4 PLACES	± ---	± ---	CHECKED BY	DATE				
				3 PLACES	± ---	± .005	R. DEROSS	11/10/05				
				2 PLACES	± .013	± .01	APPROVED BY	DATE				
				1 PLACE	± .025	± ---	R. DEROSS	11/10/05	MOLEX MOLEX INCORPORATED			
				ANGULAR ±1/2°			MATERIAL NO.	DOCUMENT NO.	SHEET NO.			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART		SD-84909-017		1 OF 1	
							THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					