




PRODUCT NO.
72206-000CA/000CALF
NOTE ⑧




NOTES:

- 1 8mm MIN CARD EJECT.
- 2 PUSH-ROD TRAVEL: 9.5mm
- 3 MATERIAL:
 - 3.1 HEADER ASSY:
PLASTIC HOUSING: LCP UL94V-0 BLACK - ABOVE PCB
PIN: PHOSPHOR BRONZE
 - 3.2 EJECT MECHANISM ASSY:
PLASTIC GUIDE: POLYPHTHARAMID UL94V-0 BLACK
PLASTIC PUSH-ROD BUTTON: POLYPHTHARAMID UL94V-0 BLACK
COVER PLATE, EJECT PLATE, LINK ARM,
PUSH ROD: STAINLESS STEEL
EMI CONTACT: PHOSPHOR BRONZE
- 4 FINISH (PIN)
UNDER PLATING: 0.5um MIN Ni
CONTACT AREA: 0.1um MIN GOLD OVER
0.5um MIN Pd-Ni
SOLDER TAIL: 2.5umMIN Sn-Pb FOR TIN LEAD OPTION
2.5umMIN PURE TIN FOR LEAD FREE OPTION


⑤ DIM "X"	4.25±0.1	3.5±0.1	5.0±0.1
	OTHERS	36,67	1,17,34,35,51,68

- 6 RECOMMENDED HOLD DOWN - 2mm SCREWS (95121-001) AND NUTS (92869-001).
RECOMMENDED SCREW TORQUE: 1.0 TO 1.5 MAX in-lbs. (1.2-1.7 cm-kgs).
- 7 SEE SHEET 3 FOR PCB LAYOUT INFORMATION.
- ⑧ ADD "H" TO PART NUMBER FOR OPTIONAL HOLD DOWN (2 PER EJECT MECHANISM).



HOLD DOWN

- 9 IF LEAD FREE P/N.THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- 10 IF LEAD FREE P/N.THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBED IN GS-22-008
- 11 LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		 Electronics FCI www.fciconnect.com		
ltr	ecn no	dr	date	linear	.X±.3			projection 	title R/A CARDBUS SINGLE DECK ASSEMBLY		
A	V60726	RHG	4/29/96		.XX±.13						
B	V60810	RHG	5/24/96	.XXX±.051							
C	V61089	RHG	7/2/96	angles	0° ±2°						
D	V70389	RHG	3/25/97	dr	R.GRAPE	4/29/96		product family		MCS	code —
E	V12164	TFG	8/16/01	enrg	D.BRANN	4/29/96		size dwg no			
F	N05-0054	WB	03/02/05	chr	D.BRANN	4/29/96	scale 1:1	A4		72206	sheet 1 of 3
				appd	D.BRANN	4/29/96					
sheet index	revision		F	F	F						
	sheet		1	2	3						


Tous droits strictement reserves. Reproduction ou communication a des tiers
interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire.
Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any
form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

FCI

B

PRODUCT NO.
72206-100CA/100CALF
NOTE ⑤



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	FCI Electronics www.fciconnect.com		
ltr	ecn no	dr	date	linear	.X±.3		projection	title	product family
F					.XX±.13				
					.XXX±.051				
				angles	0° ±2°	MM	scale	A4	72206
				dr	R.GRAPE 4/29/96				
				enr	D.BRANN 4/29/96				
				chr	D.BRANN 4/29/96				
				appd	D.BRANN 4/29/96				
sheet index	revision sheet								


ACAD

PDM: Rev:F


STATUS Released 26 Printed: Oct 12, 2010

FCI

B





P.C.B. LAYOUT



NOTES:

- ① RECOMMENDED DIAMETER IS $\phi 1.0$. FOR PROCESSES USING PASTE REFLOW, HOLE MAY BE AS SMALL AS $\phi 0.79$.
- 2 ALL TOLERANCES ± 0.15 UNLESS NOTED.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X $\pm$.3	projection		title R/A CARDBUS SINGLE DECK ASSEMBLY	
F					.XX $\pm$.13				
					.XXX $\pm$.051				
				angles	0° $\pm$ 2°	scale 1:1		product family MCS	
				dr	R.GRAPE 4/29/96			code	
				enr	D.BRANN 4/29/96			size dwg no	
				chr	D.BRANN 4/29/96			sheet	
				appd	D.BRANN 4/29/96			3 of	
sheet index	revision sheet							cage code	