




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

## REVISIONS

DWG. NO. SPC-F005 \* Effective: 7/5/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2012	A	Released	JN	1/05/09	JWM	1/05/09	JWM	1/05/09



### Specifications:

- 0.060" thick black and beige rubber, 1.50" wide, 2-layer non-smudge static dissipative rubber cup
- 3/8" wide, 24" long grey polyester tab contains electrically conductive carbon suffused fibers.
- Stretch hook and loop fastening system - 3/4" wide, black hook and loop material
- 1 megohm resistor

### Tab to cup resistance:

10E6 Ohms @ 100 volts per ANSI/ESD S4.1

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

### TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jason Nash	1/05/09
CHECKED BY:	DATE:
Jeff McVicker	1/05/09
APPROVED BY:	DATE:
Jeff McVicker	1/05/09

### DRAWING TITLE:

Heel Grounder, 24" Grounding Strap,

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	SPC23778	14N9043.dwg	A
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1